







RoHS


REV	ECN NO.	DESRPTION	DESIGN	APPROVAL	DATE
A1	NEW	新版发行			2026.07.09





4Pin 无缺口



5Pin 无缺口



6Pin 无缺口



SPECIFICATIONS

1. Current rating: 1A AC, DC
2. Temperature range: -40°C ~ +105°C
3. Insulation resistance: 100MΩ Min.
4. Withstanding voltage: 250V AC/ minute.
5. Contact resistance: 20mΩ Max.

Material:

Insulator: PA9T UL 94V-0
Contact: Phosphor Bronze or Brass
Plating: Plated Tin
Circuits: 02~20P
Mate with:XFCN P1250 series Housing
Ordering Code:

M1250RS-XXP-001
1 2

- 1.序列号
- 2.Pin位数 02-20P

No.of PIN/ROW	Dimension		
	A	B	C
2	7.60	4.50	1.25
3	8.85	5.75	2.50
4	10.10	7.00	3.75
5	11.35	8.25	5.00
6	12.60	9.50	6.25
7	13.85	10.75	7.50
8	15.10	12.00	8.75
9	16.35	13.25	10.00
10	17.60	14.50	11.25
11	18.85	15.75	12.50
12	20.10	17.00	13.75
13	21.35	18.25	15.00
14	22.60	19.50	16.25
15	23.85	20.75	17.50
16	25.10	22.00	18.75

X.±0.50	X.°±	PART NO: M1250RS-XXP-001		XFCN 兴飞连接器					
.X±0.25	.X°±								
.XX±0.15	.XX°±	TITLE: 1.25mm Crimp Style Connectors		0769-82001899					
.XXX±0.10	.XXX°±			www.xfconn.com					
UNITS:	mm	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF XFCN AND SHALL NOT BE REPRODUCED,COPIED OR CUED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF XFCN		DWG NO:					
				APPD		Chen ZhiQiang			
				CHKD		Liu Wei			
				DRAW		Chen HongJiang			
				DATE		2026.07.09			
				VIEW					
				SCALE		SHEET		REV	
				NONE		1/1		A1	