



RoHS
Compliant





REV.	ZONE	DESCRIPTION	DESIGN	DATE
B		NEW		

NOTE:


- MATERIAL:
 - HOUSING: THERMOPLASTIC,UL94V-0, COLOR:BLACK.
 - CENTER CONTACT : COPPER ALLOY.
 - GROUND CONTACT: COPPER ALLOY.
- FINISH:
 - CENTER CONTACT:GOLD PLATING.
50u" MIN. NICKEL UNDERPLATING.
 - GROUND CONTACT GOLD PLATING;
50u" MIN. NICKEL UNDERPLATING OVERALL.
- PART NUMBER DESCRIPTION:

PART NO.	DESCRIPTION
9184-000030	GROUND CONTACT GOLD PLATING;
- APPLIED TO IR SOLDERING PROCESS
- COPLANARITY: 0.10mm MAX.

PART NO.	DESCRIPTION
9184-000030	GROUND CONTACT GOLD PLATING;



RECOMMENDED PCB LAYOUT
(TOLERANCE:±0.05)



X. ±0.50	X.* ±2°	UNITS mm	广东创粤科技有限公司		
.X ±0.30	.X.* ±1°		TITLE: RF 四代天线座 黑色塑胶 金flash		
.XX ±0.10	.XX.* ±0.5°	MAT'L			
.XXX ±0.05					
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF SHENZHEN CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF SHENZHEN CHUANGYUE TECHNOLOGY CO., LTD		FINISH	APPD:	DWG NO.:	
			CHKD:	CY-IPEX4-H0.6-16106	
		Q'TY	DR:		
					SCALE SHEET REV. 1/1 1/1 A1