









RoHS
Compliant

6	7			
REV.	ZONE	DESCRIPTION	DESIGN	DATE
B		NEW		



RECOMMENDED PCB LAYOUT
(TOLERANCE: ± 0.05)

NOTE:

- MATERIAL:
 - HOUSING: THERMALPLASTIC. UL94-V0 COLOR:BLACK
 - CENTER CONTACT : COPPER ALLOY.
 - GROUND CONTACT: COPPER ALLOY.
- FINISH:
 - CENTER CONTACT GOLD PLATING.
 - GROUND CONTACT GOLD PLATING.
- APPLIED TO IR SOLDERING PROCESS.
- PART NUMBER DESCRIPTION:

PART NO	DESCRIPTION
9183-000030	GROUND CONTACT GOLD PLATING

X. ± 0.50	X.* $\pm 2^\circ$	UNITS mm	广东创粤科技有限公司		
.X ± 0.30	.X.* $\pm 1^\circ$		TITLE: RF 三代天线座 黑色塑胶 金flash		
.XX ± 0.10	.XX.* $\pm 0.5^\circ$	MAT'L			
.XXX ± 0.05					
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF SHENZHEN CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF SHENZHEN CHUANGYUE TECHNOLOGY CO., LTD		FINISH	APPD:	DWG NO.: CY-IPEX3-H0.85-16105	
			CHKD:		
		Q'TY	DR:		
				SCALE	SHEET
				1/1	1/1
					REV. A1