







RoHS

REV.	ECN NO.	DESCRIPTION	DESIGN	APPROVAL	DATE
A1	NEW	更换图框			2023.09.03



- 技术要求:
- 1.打铜底0.5-1μm,镍2-2.5μm, 镀雾锡3-5μm。
 - 2.铆好后不得有松动现象。
 - 3.插脚尖部符合可焊性要求。
 - 4.螺纹需符合通止规/止针要求。
 - 5.螺纹扭矩: 2.0Nm.
 - 6.额定电流 : 135A.



<div>>30.±0.4</div>	<div>X.°±</div>	<div>PART NO:</div> <div>TT56145145-1200</div>		<div>XFCN 兴飞连接器</div>		
<div>6-30±0.3</div>	<div>.X°±</div>					
<div>0-6±0.2</div>	<div>.XX°±</div>					
<div>ANGLES±1°</div>	<div>.XXX°±</div>	<div>TITLE:</div> <div>PCB SOLDERING TERMINAL</div>		<div>0769-82001899</div>		
<div>UNITS:</div> <div>mm</div>	<div>www.xfconn.com</div>					
<div>THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF XFCN AND SHALL NOT BE REPRODUCED, COPIED OR CUED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF XFCN</div>		<div>APPD</div> <div>Chen ZhiQiang</div>		<div>DWG NO:</div> <div>/</div>		
		<div>CHKD</div> <div>Liu Wei</div>	<div>VIEW</div>	<div></div>		
		<div>DRAW</div> <div>Chen HongJiang</div>	<div>SCALE</div>	<div>SHEET</div>	<div>REV</div>	
		<div>DATE</div> <div>2024.04.23</div>	<div>NONE</div>	<div>1/1</div>	<div>A1</div>	

2	垫片		SPCC	1
1	插脚		H62 (Y2)	1
序号	名称	零件编号	材质	数量