





THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	DRAWING REPLACES EC:503-8-OD1	9/25/14	D.FRISIELLO





WIRING MAP		
JACK A	JACK B	PLUG
1	1	1
2	2	2
3	3	3
4	4	4
5	5	5
6	6	6
7	7	7
8	8	8

**NOTES:**  
 HOUSING: ABS (UL94V-0 RATED)  
 COLOR: IVORY  
  
 CONTACTS: COPPER ALLOY  
 PLATING: 6 μINCHES GOLD  
  
 ELECTRICAL:  
 CURRENT RATING: 2 AMP (MAX)  
 VOLTAGE RATING: 140 VDC  
  
 TEMPERATURE RATING: -20°C TO 80°C.

JACKS ACCEPT KEYED PLUGS.  
 COMPONENT SHALL BE TESTED FOR CONTINUITY.  
 COMPONENT SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

**REGULATORY COMPLIANCE:**  
 CE2011/65/EU (RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0%	APPROVALS	DATE	 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	DRAWN BY DOUG PARHAM	3/8/2001	
ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5.08] .XX = ±.02 [1.51] .XXX = ±.005 [1.13]	CHECKED BY TOM CLARK	3/16/2001	CATEGORY <b>TELECOM/MODULAR</b>
	APPROVED BY RON CARRICK	3/20/2001	
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	PRODUCT DESCRIPTION <b>MOD SPLITTER(8X8)M TO 2(8X8)KF</b>	
COLOR VARIATIONS MAY OCCUR	SIZE <b>A</b>	FSCM NO. <b>43321</b>	DWG. NO. <b>EC503-8</b> SCALE: NONE   CAD FILE: EC503-8.SLDDRW   SHEET 1 OF 1