




NOTES:









- 1. Rated voltage: 250V AC/DC
- 2. Rated current: 7.5A AC DC
- 3. Contact resistance: ≤20 mΩ
- 4. Insulation resistance: ≥1000 MΩ
- 5. Withstand voltage: 1000V AC/minute
- 6. Ambient temperature: -40℃~+105℃
- 7. Material : PA66 UL94V-0 750℃
- 8. Matched RoHS criteria

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHEJIANG DELI CONNECTORS CO., LTD			
.X: ± 0.25	X°: ± 3.0°	PRODUCT NAME: DTM-2Y		TITLE: 4.19 mm Pitch Housing	
.XX: ± 0.15	.X°: ± 2.0°	DR: Yuan Jun Rong	DATE: 2025.02.22	PART NO:	
.XXX: ± 0.01	.XX°: ± 1.0°	CHKD: Wu Hui	DATE: 2025.02.22	SCALE: N/A	PAGE: 1/1
FINISH:		APPD: Ren An De	DATE: 2025.02.22	UNITS: mm	REV.: A
DRAWING NO:					


REV.	REVISION DESCRIPTION	DATE	APPD

NOTES:

1. Rated voltage: 250V AC/DC
2. Rated current: 7.5A AC/DC
3. Contact resistance: $\leq 20\text{ m}\Omega$
4. Insulation resistance: $\geq 1000\text{ M}\Omega$
5. Withstand voltage: 1000V AC/minute
6. Ambient temperature: $-40^{\circ}\text{C} \sim +105^{\circ}\text{C}$
7. Material: PA66 UL94V-0 750 $^{\circ}\text{C}$
8. Matched RoHS criteria






GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHEJIANG DELI CONNECTORS CO., LTD			
.X: ± 0.25	X°: ± 3.0°	PRODUCT NAME: DTM-3Y		TITLE: 4.19 mm Pitch Housing	
.XX: ± 0.15	.X°: ± 2.0°	DR: Yuan Jun Rong	DATE: 2025.02.22	PART NO:	
.XXX: ± 0.01	.XX°: ± 1.0°	CHKD: Wu Hui	DATE: 2025.02.22	SCALE: N/A	PAGE: 1/1
FINISH:		APPD: Ren An De	DATE: 2025.02.22	UNITS: mm	REV.: A
DRAWING NO:					




REV.	REVISION DESCRIPTION	DATE	APPD

- NOTES:
- 1. Rated voltage: 250V AC/DC
 - 2. Rated current: 7.5A AC/DC
 - 3. Contact resistance: $\leq 20\text{ m}\Omega$
 - 4. Insulation resistance: $\geq 1000\text{ M}\Omega$
 - 5. Withstand voltage: 1000V AC/minute
 - 6. Ambient temperature: $-40^{\circ}\text{C}\sim+105^{\circ}\text{C}$
 - 7. Material : PA66 UL94V-0 750℃
 - 8. Matched RoHS criteria



GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHEJIANG DELI CONNECTORS CO., LTD			
.X: ± 0.25	X°: ± 3.0°	PRODUCT NAME: DTM-4Y		TITLE: 4.19 mm Pitch Housing	
.XX: ± 0.15	.X°: ± 2.0°			PART NO:	
.XXX: ± 0.01	.XX°: ± 1.0°	DR: Yuan Jun Rong	DATE: 2025.02.22	SCALE: N/A	
FINISH: _____		CHKD: Wu Hui	DATE: 2025.02.22	PAGE: 1/1	
DRAWING NO:		APPD: Ren An De	DATE: 2025.02.22	UNITS: mm	REV.: A







- NOTES:
- 1. Rated voltage: 250V AC/DC
 - 2. Rated current: 7.5A AC/DC
 - 3. Contact resistance: $\leq 20 \text{ m}\Omega$
 - 4. Insulation resistance: $\geq 1000 \text{ M}\Omega$
 - 5. Withstand voltage: 1000V AC/minute
 - 6. Ambient temperature: $-40^{\circ}\text{C} \sim +105^{\circ}\text{C}$
 - 7. Material : PA66 UL94V-0 750 $^{\circ}\text{C}$
 - 8. Matched RoHS criteria

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHEJIANG DELI CONNECTORS CO., LTD			
.X: ± 0.25	X°: $\pm 3.0^{\circ}$	PRODUCT NAME: DTM-6Y		TITLE: 4.19 mm Pitch Housing	
.XX: ± 0.15	.X°: $\pm 2.0^{\circ}$	DR: Yuan Jun Rong	DATE: 2025.02.22	PART NO:	
.XXX: ± 0.01	.XX°: $\pm 1.0^{\circ}$	CHKD: Wu Hui	DATE: 2025.02.22	SCALE: N/A	PAGE: 1/1
DRAWING NO:		APPD: Ren An De	DATE: 2025.02.22	UNITS: mm	REV.: A

REV.	REVISION DESCRIPTION	DATE	APPD


- NOTES:
1. Rated voltage: 250V AC/DC
 2. Rated current: 7.5A AC/DC
 3. Contact resistance: $\leq 20\text{ m}\Omega$
 4. Insulation resistance: $\geq 1000\text{ M}\Omega$
 5. Withstand voltage: 1000V AC/minute
 6. Ambient temperature: $-40^{\circ}\text{C} \sim +105^{\circ}\text{C}$
 7. Material : PA66 UL94V-0 750°C
 8. Matched RoHS criteria







GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHEJIANG DELI CONNECTORS CO., LTD	
.X: ± 0.25	X°: $\pm 3.0^{\circ}$	PRODUCT NAME: DTM-8Y	TITLE: 4.19 mm Pitch Housing
.XX: ± 0.15	.X°: $\pm 2.0^{\circ}$	DR: Chen Quan Long	DATE: 2026/06/16
.XXX: ± 0.01	.XX°: $\pm 1.0^{\circ}$	CHKD: Wu Hui	DATE: 2026/06/16
FINISH: _____		APPD: Ren An De	DATE: 2026/06/16
DRAWING NO:		UNITS: mm	PAGE: 1/1
			REV.: A

REV.	REVISION DESCRIPTION	DATE	APPD

- NOTES:
- 1. Rated voltage: 250V AC/DC
 - 2. Rated current: 7.5A AC/DC
 - 3. Contact resistance: $\leq 20\text{ m}\Omega$
 - 4. Insulation resistance: $\geq 1000\text{ M}\Omega$
 - 5. Withstand voltage: 1000V AC/minute
 - 6. Ambient temperature: $-40^{\circ}\text{C} \sim +105^{\circ}\text{C}$
 - 7. Material : PA66 UL94V-0 750°C
 - 8. Matched RoHS criteria





嵌合状态



嵌合状态




GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHEJIANG DELI CONNECTORS CO., LTD	
.X: ± 0.25	X° : ± 3.0°	PRODUCT NAME: DTM-12Y	TITLE: 4.19 mm Pitch Housing
.XX: ± 0.15	.X° : ± 2.0°	DR: Chen Quan Long	DATE: 2026/06/16
.XXX: ± 0.01	.XX° : ± 1.0°	DATE: 2026/06/16	PART NO:
FINISH:		CHKD: Wu Hui	SCALE: N/A
DRAWING NO:		APPD: Ren An De	DATE: 2026/06/16
		UNITS: mm	PAGE: 1/1
			REV.: A






REV.	REVISION DESCRIPTION	DATE


- NOTES:
- Rated voltage: 250V AC/DC
 - Rated current: 7.5A AC/DC
 - Contact resistance: $\leq 20 \text{ m}\Omega$
 - Insulation resistance: $\geq 1000 \text{ M}\Omega$
 - Withstand voltage: 1000V AC/minute
 - Ambient temperature: $-40^\circ\text{C} \sim +105^\circ\text{C}$
 - Material : PA66 UL94V-0 750°C
 - Matched RoHS criteria




GENERAL TOLERANCES (UNLESS SPECIFIED)				ZHE JIANG DELI CONNECTORS CO., LTD			
.X: ± 0.25	X°: $\pm 3.0^\circ$	PRODUCT NAME: DTM-3R		TITLE: 4.19 mm Pitch Housing			
.XX: ± 0.15	.X°: $\pm 2.0^\circ$	DR: Chen Quan Long	DATE: 25/09/30	PART NO:			
.XXX: ± 0.01	.XX°: $\pm 1.0^\circ$	CHKD: Wu Hui	DATE: 25/09/30	SCALE: N/A	PAGE: 1/1		
DRAWING NO:		APPD: Ren An De	DATE: 25/09/30	UNITS: mm	REV.: A		



- NOTES:
- 1. Rated voltage: 250V AC.DC
 - 2. Rated current: 7.5A AC DC
 - 3. Contact resistance: $\leq 20\text{ m}\Omega$
 - 4. Insulation resistance: $\geq 1000\text{ M}\Omega$
 - 5. Withstand voltage: 1000V AC/minute
 - 6. Ambient temprature: $-40^{\circ}\text{C}\sim +105^{\circ}\text{C}$
 - 7. Material : PA66 UL94V-0 750 $^{\circ}\text{C}$
 - 8. Matched RoHS criteria




GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO.,LTD	
.X: ± 0.25	X° : ± 3.0°	PRODUCT NAME: DTM-4R	TITLE: 4.19 mm Pitch Housing
.XX: ± 0.15	.X° : ± 2.0°	DR:Chen Quan Long	DATE:25/09/30
.XXX: ± 0.01	.XX° : ± 1.0°	DATE:25/09/30	PART NO:
FINISH:		CHKD: Wu Hui	SCALE: N/A
DRAWING NO:		APPD: Ren An De	DATE:25/09/30
			PAGE: 1/1
			UNITS: mm
			REV.: A




- NOTES:
- 1. Rated voltage: 250V AC.DC
 - 2. Rated current: 7.5A AC DC
 - 3. Contact resistance: $\leq 20\text{ m}\Omega$
 - 4. Insulation resistance: $\geq 1000\text{ M}\Omega$
 - 5. Withstand voltage: 1000V AC/minute
 - 6. Ambient temprature: $-40^{\circ}\text{C}\sim +105^{\circ}\text{C}$
 - 7. Material : PA66 UL94V-0 750 $^{\circ}\text{C}$
 - 8. Matched RoHS criteria


GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO.,LTD			
.X: ± 0.25	X°: ± 3.0°	PRODUCT NAME: DTM-6R		TITLE: 4.19 mm Pitch Housing	
.XX: ± 0.15	.X°: ± 2.0°	DR:Chen Quan Long	DATE:25/09/30	PART NO:	
.XXX: ± 0.01	.XX°: ± 1.0°	CHKD: Wu Hui	DATE:25/09/30	SCALE: N/A	PAGE: 1/1
FINISH:		APPD: Ren An De	DATE:25/09/30	UNITS: mm	REV.: A
DRAWING NO:					



- NOTES:
- 1. Rated voltage: 250V AC/DC
 - 2. Rated current: 7.5A AC/DC
 - 3. Contact resistance: $\leq 20 \text{ m}\Omega$
 - 4. Insulation resistance: $\geq 1000 \text{ M}\Omega$
 - 5. Withstand voltage: 1000V AC/minute
 - 6. Ambient temperature: $-40^\circ\text{C} \sim +105^\circ\text{C}$
 - 7. Material : PA66 UL94V-0 750°C
 - 8. Matched RoHS criteria

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO., LTD			
.X: ± 0.25	X°: $\pm 3.0^\circ$	PRODUCT NAME: DTM-8R		TITLE: 4.19 mm Pitch Housing	
.XX: ± 0.15	.X°: $\pm 2.0^\circ$	DR: Chen Quan Long	DATE: 26/03/16	PART NO:	
.XXX: ± 0.01	.XX°: $\pm 1.0^\circ$	CHKD: Wu Hui	DATE: 26/03/16	SCALE: N/A	PAGE: 1/1
DRAWING NO:		APPD: Ren An De	DATE: 26/03/16	UNITS: mm	REV.: A





NOTES


Available in 02 Circuits.

Match with DTM-2Y series housing

Material : PA66 UL94V-0 750°C.

Color : Orange

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO .,LTD			
. X: ± 0.25	X° : ± 3.0°	PRODUCT NAME: DTM-2YS		TITLE: 4.19 mm Pitch Housing	
. XX: ± 0.15	. X° : ± 2.0°			PART NO:	
. XXX: ± 0.01	. XX° : ± 1.0°	DR:Chen Quan Long	DATE:25/09/30	SCALE: N/A	
FINISH:		CHKD: Wu Hui	DATE:25/09/30	PAGE: 1/1	
DRAWING NO:		APPD: Ren An De	DATE:25/09/30	UNITS: mm	REV.: A



REV.	REVISION DESCRIPTION	DATE	

NOTES


Available in 03 Circuits.

Match with DTM-3Y series housing

Material : PA66 UL94V-0 750°C.

Color : Orange

GENERAL TOLERANCES (UNLESS SPECIFIED)				ZHE JIANG DELI CONNECTORS CO .,LTD			
. X: ± 0.25	X° : $\pm 3.0^\circ$	PRODUCT NAME:		TITLE:			
. XX: ± 0.15	. X° : $\pm 2.0^\circ$	DTM-3YS		4.19 mm Pitch Housing			
. XXX: ± 0.01	. XX° : $\pm 1.0^\circ$	DR:Chen Quan Long	DATE:25/09/30	PART NO:			
FINISH:		CHKD: Wu Hui	DATE:25/09/30	SCALE: N/A		PAGE: 1/1	
DRAWING NO:		APPD: Ren An De	DATE:25/09/30	UNITS: mm		REV. : A	




REV.	7	REVISION DESCRIPTION	8	DATE

NOTES

Available in 06 Circuits.
Match with DTM-6Y series housing
Material : PA66 UL94V-0 750°C.
Color : Orange

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO ., LTD			
. X: ± 0.25	X° : $\pm 3.0^\circ$	PRODUCT NAME: DTM-6YS		TITLE: 4.19 mm Pitch Housing	
. XX: ± 0.15	. X° : $\pm 2.0^\circ$			PART NO:	
. XXX: ± 0.01	. XX° : $\pm 1.0^\circ$	DR:Chen Quan Long	DATE:25/09/30	SCALE: N/A	
FINISH:		CHKD: Wu Hui	DATE:25/09/30	PAGE: 1/1	
DRAWING NO:		APPD: Ren An De	DATE:25/09/30	UNITS: mm	REV.: A



REV.	REVISION DESCRIPTION	DATE	

NOTES


Available in 08 Circuits.

Match with DTM-8Y series housing

Material : PA66 UL94V-0 750°C.

Color : Orange



GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO .,LTD	
. X: ± 0.25	X° : ± 3.0°	PRODUCT NAME: DTM-8YS	TITLE: 4.19 mm Pitch Housing
. XX: ± 0.15	. X° : ± 2.0°		
. XXX: ± 0.01	. XX° : ± 1.0°	DR:Chen Quan Long	DATE:26/06/16
FINISH:		CHKD: Wu Hui	DATE:26/06/16
DRAWING NO:		APPD: Ren An De	DATE:26/06/16
			SCALE: N/A
			PAGE: 1/1
			UNITS: mm
			REV.: A



NOTES

Available in 12 Circuits.
Match with DTM-12Y series housing
Material : PA66 UL94V-0 750°C.
Color : Orange


GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO .,LTD			
. X: ± 0.25	X° : ± 3.0°	PRODUCT NAME: DTM-12YS		TITLE: 4.19 mm Pitch Housing	
. XX: ± 0.15	. X° : ± 2.0°			PART NO:	
. XXX: ± 0.01	. XX° : ± 1.0°	DR:Chen Quan Long	DATE:26/06/16	SCALE: N/A	
FINISH:		CHKD: Wu Hui	DATE:26/06/16	PAGE: 1/1	
DRAWING NO:		APPD: Ren An De	DATE:26/06/16	UNITS: mm	REV.: A



NOTES:


1. Rated voltage: 250V AC.DC
2. Rated current: 7.5A AC DC
3. Contact resistance: $\leq 20 \text{ m}\Omega$
4. Insulation resistance: $\geq 1000 \text{ M}\Omega$
5. Withstand voltage: 1000V AC/minute
6. Ambient temprature: $-40^{\circ}\text{C} \sim +105^{\circ}\text{C}$
7. Material : PA66 UL94V-0 750 $^{\circ}\text{C}$
8. Matched RoHS criteria

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO .,LTD	
.X: ± 0.25	X° : $\pm 3.0^{\circ}$	PRODUCT NAME: DTM-2RS	TITLE: 4.19 mm Pitch Housing
.XX: ± 0.15	.X° : $\pm 2.0^{\circ}$		
.XXX: ± 0.01	.XX° : $\pm 1.0^{\circ}$	DR:Chen Quan Long	DATE:25/09/30
FINISH:		CHKD: Wu Hui	DATE:25/09/30
DRAWING NO:		APPD: Ren An De	DATE:25/09/30
		SCALE: N/A	PAGE: 1/1
		UNITS: mm	REV.: A




- NOTES:
- 1. Rated voltage: 250V AC. DC
 - 2. Rated current: 7.5A AC DC
 - 3. Contact resistance: $\leq 20\text{ m}\Omega$
 - 4. Insulation resistance: $\geq 1000\text{ M}\Omega$
 - 5. Withstand voltage: 1000V AC/minute
 - 6. Ambient temprature: $-40^{\circ}\text{C}\sim +105^{\circ}\text{C}$
 - 7. Material : PA66 UL94V-0 750°C
 - 8. Matched RoHS criteria

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO ., LTD			
. X: ± 0.25	X° : $\pm 3.0^{\circ}$	PRODUCT NAME: DTM-3RS		TITLE: 4.19 mm Pitch Housing	
. XX: ± 0.15	. X° : $\pm 2.0^{\circ}$			PART NO:	
. XXX: ± 0.01	. XX° : $\pm 1.0^{\circ}$	DR:Chen Quan Long	DATE:25/09/30	SCALE: N/A	
FINISH:		CHKD: Wu Hui	DATE:25/09/30	PAGE: 1/1	
DRAWING NO:	QC-DTM-3RS	APPD: Ren An De	DATE:25/09/30	UNITS: mm	REV.: A




- NOTES:
- 1. Rated voltage: 250V AC.DC
 - 2. Rated current: 7.5A AC DC
 - 3. Contact resistance: $\leq 20\text{ m}\Omega$
 - 4. Insulation resistance: $\geq 1000\text{ M}\Omega$
 - 5. Withstand voltage: 1000V AC/minute
 - 6. Ambient temprature: $-40^{\circ}\text{C} \sim +105^{\circ}\text{C}$
 - 7. Material : PA66 UL94V-0 750 $^{\circ}\text{C}$
 - 8. Matched RoHS criteria

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO .,LTD			
. X: ± 0.25	X° : $\pm 3.0^{\circ}$	PRODUCT NAME: DTM-6RS		TITLE: 4.19 mm Pitch Housing	
. XX: ± 0.15	. X° : $\pm 2.0^{\circ}$			PART NO:	
. XXX: ± 0.01	. XX° : $\pm 1.0^{\circ}$	DR:Chen Quan Long	DATE:25/09/30	SCALE: N/A	
FINISH:		CHKD: Wu Hui	DATE:25/09/30	PAGE: 1/1	
DRAWING NO:		APPD: Ren An De	DATE:25/09/30	UNITS: mm	REV.: A




- NOTES:
- 1. Rated voltage: 250V AC/DC
 - 2. Rated current: 7.5A AC/DC
 - 3. Contact resistance: $\leq 20\text{ m}\Omega$
 - 4. Insulation resistance: $\geq 1000\text{ M}\Omega$
 - 5. Withstand voltage: 1000V AC/minute
 - 6. Ambient temperature: $-40^{\circ}\text{C}\sim +105^{\circ}\text{C}$
 - 7. Material : PA66 UL94V-0 750°C
 - 8. Matched RoHS criteria

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO.,LTD			
.X: ± 0.25	X° : $\pm 3.0^{\circ}$	PRODUCT NAME: DTM-8RS		TITLE: 4.19 mm Pitch Housing	
.XX: ± 0.15	.X° : $\pm 2.0^{\circ}$			PART NO:	
.XXX: ± 0.01	.XX° : $\pm 1.0^{\circ}$	DR:Chen Quan Long	DATE:26/03/16	SCALE: N/A	
FINISH:		CHKD: Wu Hui	DATE:26/03/16	PAGE: 1/1	
DRAWING NO:		APPD: Ren An De	DATE:26/03/16	UNITS: mm	REV.: A



- NOTES:
- 1. Rated voltage: 250V AC/DC
 - 2. Rated current: 7.5A AC/DC
 - 3. Contact resistance: $\leq 20 \text{ m}\Omega$
 - 4. Insulation resistance: $\geq 1000 \text{ M}\Omega$
 - 5. Withstand voltage: 1000V AC/minute
 - 6. Ambient temperature: $-40^{\circ}\text{C} \sim +105^{\circ}\text{C}$
 - 7. Material : PA66 UL94V-0 750°C
 - 8. Matched RoHS criteria

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO., LTD			
.X: ± 0.25	X°: $\pm 3.0^{\circ}$	PRODUCT NAME:		TITLE:	
.XX: ± 0.15	.X°: $\pm 2.0^{\circ}$	DTM-12RS		4.19 mm Pitch Housing	
.XXX: ± 0.01	.XX°: $\pm 1.0^{\circ}$	DR: Chen Quan Long	DATE: 26/03/16	PART NO:	
FINISH:		CHKD: Wu Hui	DATE: 26/03/16	SCALE: N/A	PAGE: 1/1
DRAWING NO:		APPD: Ren An De	DATE: 26/03/16	UNITS: mm	REV.: A




REV.	REVISION DESCRIPTION	DATE	APPD

NOTES:
Rated voltage: 250V AC/DC
Rated current: 7.5A AC/DC
Contact resistance: ≤20 mΩ
Insulation resistance: ≥1000 MΩ
Withstand voltage: 1000V AC/minute
Ambient temperature: -40℃~+105℃
Wire range: AWG#22~#16
Materials: Phosphor bronze, Tin plated

Product name	Dimension mm				适用线规
	A1	B1	A2	B2	AWG#
DTM-T	3.4	2.8	3.2	3.5	22-20
DTM-T-G	4.4	3.4	3.2	3.5	18-16

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHEJIANG DELI CONNECTORS CO., LTD			
.X: ± 0.25	X°: ± 3.0°	PRODUCT NAME: DTM-T		TITLE: 4.19mm Pitch Wire To Wire Crimp Terminal	
.XX: ± 0.15	.X°: ± 2.0°			PART NO:	
.XXX: ± 0.01	.XX°: ± 1.0°	DR: Chen Quan Long	DATE: 2025.02.22	SCALE: N/A	
FINISH:		CHKD: Wu Hui	DATE: 2025.02.22	PAGE: 1/1	
DRAWING NO:		APPD: Ren An De	DATE: 2025.02.22	UNITS: mm	REV.: A



REV.	REVISION DESCRIPTION	DATE	APPD

NOTES:
Rated voltage: 250V AC.DC
Rated current: 7.5A AC DC
Contact resistance: ≤20 mΩ
Insulation resistance: ≥1000 MΩ
Withstand voltage: 1000V AC/minute
Ambient temprature:-40℃~+105℃
Wire range: AWG#22~#16
Materials: Phosphor bronze,Tin plated

Product name	Dimension mm				适用线规
	A1	B1	A2	B2	AWG#
DTM-RT-G	4.3	3.3	3.2	3.5	18-16
DTM-RT	3.4	2.8	3.2	3.5	22-20

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHEJIANG DELI CONNECTORS CO.,LTD			
.X: ± 0.25	X° : ± 3.0°	PRODUCT NAME: DTM-RT		TITLE: 4.19mm Pitch Wire To Wire Crimp Terminal	
.XX: ± 0.15	.X° : ± 2.0°			PART NO:	
.XXX: ± 0.01	.XX° : ± 1.0°	DR:Chen Quan Long	DATE:2025.02.22	SCALE: N/A	
FINISH:		CHKD:Wu Hui	DATE:2025.02.22	PAGE: 1/1	
DRAWING NO:		APPD:Ren An De	DATE:2025.02.22	UNITS: mm	REV.: A