





SK — 12D07 — [X] [X] — [X]

Knob Type
L
G
V

H (mm)
2 ~ 12

Colour
B:Black
R:Red





G TYPE	L TYPE	V TYPE
		

		——				——
		——				——
		——				——
④	Terminal	——	3	Brass（0.30t）	ag Plated	——
③	Base	——	1	Phenolic Resin		——
②	Cover	——	1	Sus	Natural	——
①	Keystake	——	1	Pa66	Black	——
ITEM	PAPT NAME	TER,NO	QTY	MATERIAL	FINISHING	REMARK

RATING	0.3A 50V DC
CIRCUIT	1P2T
CONTACT RESISTANCE	100m MAX.
TRAVEL	2mm
OPERATING FORCE	250±100gf
OPERATING LIFE(cycles)	10,000

MARK	DESCRIPTION	DATE	REVISED	APPROVED
Δx				
Δx				
Δx				

REVISIONS

UNSPECIFIED TOLERANCES	
ANGLAR	±5°
L≤4	±0.2
4<L≤16	±0.3
16<L≤63	±0.4
L>63	±0.5

DSND		DATE		SCALE: N/A
DWN		DATE		VIEW:
CHKD		DATE		UNIT: mm
APPD		DATE		SIZE: A4

XKB INDUSTRIAL PRECISION CO.,LIMITED

MODEL TYPE: SLIDE SWITCH

PART NO.: SK-12D07

DWG NO.: SK-12D07-X-X

WEIGHT	SHEET	REVISION
1.0g	1/1	A0

www.xk-dg.cn www.1k0k.com www.1k0k.cn