





PCB.焊接图
PCB.WELDING DRAWING




NOTES:
1.Rat voltage:12VDC 50mA
1.额电压：12VDC 50mA
2.Contact Resistance:≤100mΩ Max
2.接触电阻：≤100mΩ
3.Operating Force:260±50gf
3.操作力：260±50gf
4.Travel：0.25±0.1mm
4.行程：0.25 + 0.1mm
5.Insulation Resistance:≥100MΩ
5.绝缘电阻：≥100MΩ
6.Dielectric strength：≥250VAC
6.介电强度：≥250VAC
7.Life：30,000 times
7.寿命：30,000 times
8.Operating Temperature:-20℃±80℃
8.使用温度：-20℃±80℃







电路图
CIRCUIT DIAHRAM






| NO 序号 | Part name 部件名 | Material 材料 | QTY 数量 | Remark 备注 |
|---|---|---|---|---|
| 5 | Push-Button 按钮 | PPA | 1 | Black 黑色 |
| 4 | Blind flange 盖板 | SUS | 1 | |
| 3 | Shrapnel 弹片 | SUS | 1 | Ag plating 镀银 |
| 2 | Noumenon 本体 | PPA | 1 | Black 黑色 |
| 1 | Card 卡件 | Brass | 1 | Ag plating 镀银 |

| REV | DATE | REVISION DESCRIPTION | ISSUE |
|---|---|---|---|
| A4 | | | |
| A3 | | | |
| A2 | | | |
| A1 | | | |

台普 ROCPU

| COMMON TOLERANCE | |
|---|---|
| X.XX | ± 0.10 |
| X.X | ± 0.15 |
| X | ± 0.25 |
| ANGULAR | —— |

| | | | | |
|---|---|---|---|---|
| UNIT | MM | PROJCTED | | PRODUCT NAME: |
| DRAWN BY | FUYUAN | CHECKED BY | COCO | MODEL NO: TP11822620 |
| DATE | 2019 | APPROVAL B | ALEN | Https: www.rocpu.tw |

# ROCPU TECHNOLONGY CO.,LTD

Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission