

② Order Code:

A-M08A04FOExxx02BK00

L:
050: 500mm ±20mm
100: 1000mm ±30mm
200: 2000mm ±50mm
500: 5000mm ±100mm

Notes:

Detailed Product Description:

1.Waterproof connector rating is IP67/IP68
2.Protected from dust and water during immersion, resistant to many oils and chemical etc.
3. Outer Jacket material : PUR Black

Other Specification:

4.Rating voltage: 60V AC/DC
5.Rating current: 3A
6.Insulation resistance: >100MΩ.
7.Contact resistance of connector: ≤10mΩ.
8.Operating Temperature: -25°C ~ +85°C.

WIRE LIST

P1	COLOR	P2
1	BROWN	OPEN
2	WHITE	
3	BLUE	
4	BLACK	

ITEM	SPECIFICATION	Q'TY	UNIT
4	HD PE	3	G
3	BLACK PUR	6	G
2	M8 A CODING 4P/F CONNECTOR	1	SET
1	UL20549 24AWG*4C JACKET BLACK PUR OD=5.0mm	1	PCS

RoHS compliant

Unit: mm

Scale	Free
TOLERANCE	
.X	±0.5
.XX	±0.20
DIM	TOL
X.	±2.0°
.X	±1.0°
Angle	TOL

Id.	Modification	Date	Name
②	Add the order code	31.05.2023	Winnie
①	Update the P/N	26.01.2019	Segal
⓪	Drawn	21.11.2018	Segal

	Date	Name
Drawn	21.11.2018	Segal
Approved	31.05.2023	Winnie

ASSMANN WSW components

Customer-No.

ASSMANN WSW-No.

① A-M08A04FOExxx02BK00

Drawing-No.

ASS 8411 CA

rev02

Replace

Sheet