

缺第17-22,29,32,33,36,37P







PCB LAYOUT

NOTE:

MATERIAL

HOUSING: PA6T UL94V-0

CONTACT: H65.

CONTACT PLATING: GOLD.

ELECTRICAL

CURRENT RATING: 3AMP.

VOLTAGE RATING: 250VAC/DC.

DIELECTRC WITHSTANDING VOLTAGE:600VAC MIN.

CONTACT RESISTANCE: 20mΩMAX.

INSULATION RESISTANCE:1000MΩMIN.

ENVIRONMENTAL

TEMPERATURE RANGE: -40° CTO+105° C.

DIMENSION TABLE: 注：2*40P A尺寸不用减0.25mm

Circuits	Dimension		Circuits	Dimension		Circuits	Dimension	
	A	B		A	B		A	B
2 * 2	5.08	2.54	2 *15	38.10	35.56	2 *28	71.12	68.58
2 * 3	7.62	5.08	2 *16	40.64	38.10	2 *29	73.66	71.12
2 * 4	10.16	7.62	2 *17	43.18	40.64	2 *30	76.20	73.66
2 * 5	12.70	10.16	2 *18	45.72	43.18	2 *31	78.74	76.20
2 * 6	15.24	12.70	2 *19	48.26	45.72	2 *32	81.28	78.74
2 * 7	17.78	15.24	2 *20	50.80	48.26	2 *33	83.82	81.28
2 * 8	20.32	17.78	2 *21	53.34	50.80	2 *34	86.36	83.82
2 * 9	22.86	20.32	2 *22	55.88	53.34	2 *35	88.90	86.36
2 *10	25.40	22.86	2 *23	58.42	55.88	2 *36	91.44	88.90
2 *11	27.94	25.40	2 *24	60.96	58.42	2 *37	93.98	91.44
2 *12	30.48	27.94	2 *25	63.50	60.96	2 *38	96.52	93.98
2 *13	33.02	30.48	2 *26	66.04	63.50	2 *39	99.06	96.52
2 *14	35.56	33.02	2 *27	68.58	66.04	2 *40	101.60	99.06

RoHS2.0

本圖紙知識產權及版權由深圳市永丰盈电子有限公司所有,未經書面許可不准擅自傳閱、复制和修改.本公司保留法律追究的权利。

类 别	针座	品 名	CS-1107-2X20 N17-22,29, 32,33,36,37(L11/16)	X.	±0.50	材 料		单 位	mm	SHEET 1 OF 1		
版 本	A/0	设 计	李文畅	X.X	±0.20	颜 色		比 例	1:1	⚠	修改内容	修改日期
制定部门	工程部	绘 制	李文畅	X.XX	±0.10	画 法		数 量		1		
工程图号	CST-1107	审 核	姚培柱	X.XXX	±0.05	CST 深圳市永丰盈电子有限公司 ShenZhenYongFengYing ELEECTRONICS CO.,LTD.				2		
制定日期	2019/06/06	核 准	周中湖	X.XXXX	±0.01					3		