




e-Socket

The e-Socket is a socket which is used together with e-WriterPro. MCUs with the same package types can use the same e-Socket for programming. It is not necessary to purchase individual programming adaptors for different MCUs. The e-Socket is designed with a programming counter which enables the e-WriterPro to remind users when to replace the e-Socket with a new one after a certain amount of times. This function is provided to maintain high programming quality.



Item	Box content item name	Number
1	e-Socket	1

※ Combined products and optional accessories: e-WriterPro (/e-writerpro)

No.	Product Name	Supported Package	Suggested Programming Times
1	ESKT6S0TC	SOT23-6	10,000
2	ESKT6DFNC	6DFN(2mm*2mm*0.75mm)	10,000
3	ESKT8SOP-RF	8SOP-EP(Used for BC2102,BC2161)	10,000
4	ESKT10SOPC	10SOP	10,000
5	ESKT10MSOPA	8MSOP, 10MSOP	10,000
6	ESKT16NSOP-RF	16NSOP-EP(Used for BC2161)	10,000
7	ESKT16NSOPC	8SOP, 14SOP, 16NSOP(Applicable beside the HT48RA0-6 series MCU)	10,000
8	ESKT16NSOPHIRCA	16NSOP (for HT48RA0-6 only)	10,000
9	ESKT16QFNA	16QFN(3mm*3mm*0.75mm)	5,000
10	ESKT16QFN4C	16QFN(4mm*4mm*0.75mm)	5,000
11	ESKT20NSOPC	20NSOP	10,000
12	ESKT20QFN4A	20QFN(4mm*4mm*0.75mm)	5,000
13	ESKT20QFN5A	20QFN(5mm*5mm*0.75mm)	5,000
14	ESKT20TSSOPA	16TSSOP, 20TSSOP	10,000
15	ESKT24QFN3C	24QFN(3mm*3mm*0.55mm)	5,000
16	ESKT24QFN4C	24QFN(4mm*4mm*0.75mm)	5,000
17	ESKT28QFN4C	28QFN (4mm*4mm*0.75mm)	5,000
18	ESKT28SSOPC	16SSOP(150mil),20SSOP(150mil), 4SSOP(150mil), 28SSOP(150mil) (Applicable beside the HT48RA0-6 series MCU)	10,000
19	ESKT28SSOPHIRCA	20SSOP (for HT48RA0-6 only)	10,000
20	ESKT28SOPD	16SOP, 18SOP, 20SOP, 24SOP, 28SOP	10,000
21	ESKT30SSOPA	20SSOP(209mil),24SSOP(209mil), 28SSOP(209mil)	10,000
22	ESKT32LQFPA	32LQFP(7mm*7mm)	10,000
23	ESKT32QFNA	32QFN(5mm*5mm*0.75mm)	5,000
24	ESKT40DIPC	8DIP, 16DIP, 18DIP, 20DIP, 22SKDIP, 24SKDIP, 28SKDIP,40DIP	25,000
25	ESKT40QFN6A	40QFN(6mm*6mm*0.75mm)	5,000
26	ESKT44QFPA	44LQFP(FP 3.2mm), 44QFP(10mm*10mm)	10,000

(/nome)			
27	ESKT44LQFPC	44LQFP(FP2.0mm)	10,000
28	ESKT46QFNC	46QFP(6.5mm*4.9mm*0.75mm)	10,000
29	ESKT48QFNA	48QFN(7mm*7mm*0.75mm)	5,000
30	ESKT48LQFPA	48LQFP(7mm*7mm)(Applicable beside the HT48RA0-6 series MCU)	10,000
31	ESKT48LQFPHIRCA	48LQFP(7mm*7mm)(for HT49RA0-6 only)	10,000
32	ESKT52QFPA	52QFP(14mm*14mm)	10,000
33	ESKT52LQFPA	52LQFP(14mm*14mm)	10,000
34	ESKT56SSOPA	48SSOP, 56SSOP	10,000
35	ESKT64LQFP7C	64LQFP(7mm*7mm)	5,000
36	ESKT64LQFP10A	64LQFP(10mm*10mm)	10,000
37	ESKT80LQFPA	80LQFP(10mm*10mm)	10,000
38	ESKT100QFPA	100QFP(14mm*20mm)	5,000
39	ESKT100LQFPA	100LQFP(14mm*14mm)	5,000
40	ESKT128QFPA	128QFP(14mm*20mm)	10,000
41	ESKT128LQFPC	128LQFP(14mm*14mm)	10,000
42	ESKT144LQFPA	144LQFP(20mm*20mm)	5,000

※ Data in parentheses next to each package type shows the actual width of the IC package.

※ ESKXXXXXC/ESKXXXXXD are compatible with ESKXXXXXA.

- Support ()
- Media Center (/en/news)
- Investor Relations (/en/investor_relations)
- Careers (/humanresource)
- Customer Service (/en/question)
- Application Notes (/en/general)
- Corporate News (/en/corporatenews)
- Financial Statement (/monthly_revenues)
- Job Opportunity (/humanresource)
- Comments & Questions (/en/question)
- Applications (/en/applications)
- Product News (/en/productnews)
- University Program (/project_purpose)
- Authorized Distributor and Agent (/en/authorized-distributor-and-agent)
- Literature (/en/demo_board)
- Holtek Channel (/en/channel)
- Shareholder's Services (/shareholders_meeting)
- Tool Maintenance (/en/tools)
- Publications (/en/publications)
- Events (/en/events)
- Stock Services (/en/stock_services)
- Calendar (/en/calendar)
- Contact IR (/en/contacts)
- Flash News Subscribe (/en/service/subscrib)
- Authorized Use Only (/en/authorized-use-only)
- Sample and buy (USA only) (http://holtekusa.com)

