





General Specification
Current Rating:1.5A DC /Contact, 20mA DC for LED signals
Voltage Rating:125V AC /Contact, 2.0 volts DC for LED signals
Operating Environment
Standard Temperature: -20℃~+70℃
Industrial Temperature: -40℃~+85℃
Humidity: 20~70%
Contact Resistance:≤30mΩ
Insulation Resistance:≥500MΩ
Dielectric Strength:500V AC/(50HZ)/Min
Mating And Unmating Force:3~20N
Durability:750 Cycles Min

Material Specification
Housing :Thermo-plastic, UL94V-0.
Contact :Alloy Copper
Shield :Alloy Copper
Please refer to the customer drawing when customer has specified





序号	名 称	材 料	数 量	镀层/颜色	备 注
6	外 壳	H62	1	NI	
5	LED灯	树脂/FE	8	NI/AG	
4	插 针	PHOSPHOR BRONZE	32	FU"	
3	中分体	PA46	2	BLACK	
2	右分体	PA46	1	BLACK	
1	左分体	PA46	1	BLACK	

版次	变 更 履 历	变更单号	绘 制	日 期
A/0	新 出 版 发 行			

网络插座外形图

绘 图: 日 期:
审 核: 日 期:
核 准: 日 期:

温州瑞川电子有限公司
WEN ZHOU RUI CHUAN ELECTRONIC CO.,LTD.

一般公差	
30~	±0.25
10~30	±0.20
~10	±0.15
角 度:	±2°
页 面:	1 of 1

品 名: RCH-56-31-14(带灯带弹)
料 号: 563114-8YG02610AB30 (RC00966)
型 号: RJ45 图 号:
版本: 单位:mm 比例: 1:1 纸张: A4

该 图 面 供 温 州 瑞 川 电 子 有 限 公 司 内 部 使 用, 不 得 私 自 复 印