Dept	Qty
DC	1
ED	1
IE	1
ISO	1
PD	1
R&D	1
SD	1
QA	1
QC	1
QE	1

晨翔2.54mm FD插头，26PIN，黑色胶芯，半金镍端子，无Kink脚

晨翔料号：DS1018-262BX

REV.	DESCRIPTION	DRAWN	CHECKED	APPROVED
A	NEW RELEASE	JLZ 06/18/24'		





PCB孔位尺寸参考
公差:±0.05

备注：
1. 电性说明：
   1.1 接触阻抗：20毫欧最大
   1.2 耐压：600伏交流电一分钟
   1.3 绝缘阻抗：1000兆欧最小
   1.4 额定电流：3安
2. 环境特性：
   2.1 工作温度：-40~+105° C
3. 材料：
   3.1 端子：黄铜,焊接区镍底镀金
   3.2 胶芯：PBT，黑色，阻燃

GENERAL TOLERANCE		ANGLE TOLERANCE	
X.	±0.60	X.	±5°
.X	±0.38	.X	±3°
.XX	±0.25	.XX	±2°

DRAWING TYPE	CUSTOMER		
SCALE	1:1	SHEET	1 OF 1
DRAWING NO.	C-DS1018-XXXXX-A		

PROJECTION		TITLE	I.D.C DIP PLUG PITCH 2.54mm
UNITS	mm		
SHEET SIZE	A4	SERIES	DS1018 SERIES

晨翔电子有限公司
CONNFLY CONNFLY ELECTRONIC CO. LTD

The information provided herein is from CONNFLY Electronic Co., Ltd. and is confidential. Any disclosure to a party other than the recipient is prohibited. The intellectual properties and its rights contained herein, including but not limited to, trademarks, patents, copyrights, trade secrets, and technical know-how, are owned exclusively by CONNFLY or its affiliates. Unauthorized use or modification is strictly prohibited without prior written consent from CONNFLY. All intellectual properties provided herein are for reference purposes only and does not constitute authorization of its use in any format or manner. CONNFLY may enforce its intellectual property rights at its own discretion; failures or delays to exercise such rights does not constitute a waiver of such rights.