SAMZO | REAC/ROHS

REV	ECN NO	DESRIPTION	DESIGN	APPROVAL	DATE
A1	NEW	Replace frame			2018.06.12









P.C.B LAYOUT
BOTTOM VIEW

3	C	1	2	7	B	A	A	*	*	*	A	A
Ⓐ		Ⓑ			Ⓒ	Ⓓ	Ⓔ	Ⓕ			Ⓖ	Ⓗ

注:"*"表示关键尺寸（4个）.

A.系列:3C-3P-1210系列
B:模具号:127-D12.7
C.引脚规格:B-三脚
D.贴装方式:A-立式插件
E.操作挡位:A-两档
F:手柄高度:020-2.0/050-5.0mm/100-10.0mm（2-12mm）
G:固定方式:A-无柱
H:物料编码:A-常规(确认待编）



SCHEMATIC(NON-SHORTING)

Typical Specifications
1.Rating:AC 125V 3A
2.Insulation Resistance:1,000M min
3.Dielectric strength:1,500V RMS
4.Operating Life: 10,000 cycles

ITEM	DESCRIPTION	MATERIAL	QTY	FINSH/COLOR					
6	STEEL BALL	STEEL	1	NATURAL					
5	SPRING	STEEL WIRE	1	NATURAL				GENERAL TOLERANCE	
4	CONTACT	BRASS STRIP	1	Ag PLATED				≥0~2<	±0.15
3	TERMINAL	BRASS STRIP	3	Ag PLATED	DESIGN	WANGGUIFA	2018.06.12	≥2~5<	±0.25
2	COVER	SUS	1	NATURAL	CHECKED	ZHENGUILAN	2018.06.12	≥0~2<	±0.15
1	KNOB.CASE	PA66	1	BLACK	APPROVED	LILIANJIANG	2018.06.14	≥5	±0.35

FIRST VIEW



SCALE 1:1 UNIT mm

The copyright belongs to samzo parts [China] Co., Ltd. please use the material after samzo parts agree to authorize. The final right of interpretation belongs to samzo parts.
WWW.KKK-JP.COM

SAMZO COMPONENTS
Electronic switch and connector manufacturer

TITLE:: 立式直插-3P(H)
DWG NO: 3C127BA-P312
PART NO: 3C1271210
MODEL NO: 3C127BAA-***-AA
NAME: SLIDE SWITCH