RoHS

















PCB

Specification:

1. Rating :125V/1.5A max
2. Contact resistance:40mΩ Max
3. Insulation resistance:500MΩMin
4. Withstand voltage: AC500V
5. Salt Spray:8±0.5H

NO.	DESCRIPTION	Q'TY	MATERIAL	REMARK
③	TERMINAL	1	Phosphor Bronze T=0.3mm	Au Sn plating
②	After the plug	1	PBT Black	
①	Housing	1	PBT 114C yellow	

SHENZHEN FUGANG TECHNOLOGY CO.,LTD						
DRAWIN	LPJ	DATE	22.07.06			RJ45 JACK
CHECKED	/	DATE	/	PROPORTION	WEIGHT	RJ-052C-2-6-114C
APPROVE	L G	DATE	22.07.06			