203M018-19B08 Product Details

203M018-19B08

TE Internal Number: 102431-000

Active

Braid, Fixed, Spin and Tinel Lock Adapters

Not EU RoHS or ELV Compliant

Product Highlights:

- Applies To Cable
- Military Style Number = MIL-C-26482
- Style = Braided
- Connector Code = 54
- Straight

View all Features

Quick Links

- Pricing & Availability
- Search for Tooling
- Product Feature Selector
- Contact Us About This Product

Add to My Part List | Request Sample | Find Similar Products | Buy Product

Documentation & Additional Information

Product Drawings:

- Adapter, Shield, Straight Code 54 (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

List all Documents

Related Products:

- Tooling

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Style = Braided
- Angle = Straight
- Connector Shell Size = 18
- Finish = Cadmium Plating over Electroless Nickel
- Color = Olive Drab

Dimensions:

- Boot Diameter (mm [in]) = 17.90 [0.705]

Body Features:

- Connector Code = 54
- Entry Size = 8
- Material = Aluminium Alloy

Configuration Features:

- Braid = Preattached Single 36 AWG Braid

Industry Standards:

- Military Style Number = MIL-C-26482
- RoHS/ELV Compliance = Not ELV/RoHS compliant
- Lead Free Solder Processes = Not relevant for lead free process

Conditions for Usage:

- Applies To = Cable

Other:

- Brand = Raychem
- Comment = For Specific shell size information, refer to Harnware™ or Catalouge.

© 2014 TE Connectivity Ltd. family of companies. All Rights Reserved