SAMZO | REAC/ROHS

REV	ECN NO	DESRIPTION	DESIGN	APPROVAL	DATE
A1	NEW	Replace frame			2020.06.12



RBCOMMENDBD P.C.B PATTBRN LAY OUT

规格说明:Specifications:

电气特性:Electrical:

1. 额定电流：Current Rating
   1.5A/contact terminal
2. 额定电压：Voltage Rating
   30V DC
3. 接触阻抗:Contact Resistance
   30 milliohms MAX
4. 耐电压:Dielectnic Withstanding Voitage:
   500 V AC AT Sea Levol
5. 绝缘阻抗:Lnsulation Resistance:
   1000MEGA ohms MIN

物理性能:Mechanical:

1. 插拔力：Cnnector Mate and Unmate Force
   Mate force:3.57kgf(MAX)
   Unmate force:1.02kgf(MIN)
2. 端子保持力：Terminal Retenion
   1.2kgf(MIN)

UNSAATEEYA

- Code: A01.
- Interface: Curled edge.
- Lifetime: 1,500 cycles.
- Material: Iron plated with nickel.
- Type: Without pillar.
- Appearance size: 14.2mm.
- Mounting method: Vertical plug-in board.
- Specification: 4+4 pins.
- Series: USB2.0 double-layer female socket.

ITEM	DESCRIPTION	MATERIAL	QTY	FINSH/COLOR					
C	塑胶	LCP	1	白色	DESIGN	WANGGUIFA	2020.06.12	≥2~5<	±0.25
B	端子	黄铜H65	1	焊接镀锡 接触镀金	CHECKED	ZHENGUILAN	2020.06.12	≥0~2<	±0.15
A	外壳	C2680/SPCC	1	镀 镍	APPROVED	LILIANJIANG	2020.06.14	≥5	±0.35

GENERAL TOLERANCE

≥0~2<	±0.15

FIRST VIEW

SCALE	1:1	UNIT	mm

The copyright belongs to samzo parts [China] Co., Ltd. please use the material after samzo parts agree to authorize. The final right of interpretation belongs to samzo parts.
WWW.KKK-JP.COM

SAMZO COMPONENTS
Electronic switch and connector manufacturer

TITLE:: USB AF 双层直插14.2mm无脚

DWG NO：UNSAA-P2011032

PART NO：UNSAA20301210

MODEL NO：UNSAATEEYA

NAME: HDMI CONN