


# SPECIFICATIONS

| | |
|---|---|
| Current Rating: | 3Amps |
| Insulation Resistance: | 1000MΩ Min |
| Contact Resistance: | 20MΩ Max |
| Withstanding Voltage: | AC 1000V |
| Operation Temperature: | -40° to+105° |
| Contact Material: | Brass |
| Standard: | PA6T |
| Insrlator Material: | Polyester(UL 94V-0) |
| Contact Plating: | Gold Flash |
| Max.Processing Temp: | 240° C for30-60seconds (260° C for5seconds) |










RECOMMEND P.C.B LAYOUT

PCB TOLERANCE:±0.05 (TOP VIEW)

深圳市韩下电子有限公司

| UNLESS OTHEWIXE SPECIFIED TOLERANCE | | | |
|---|---|---|---|
| X | :±0.30 | X° | :±5° |
| X.X | :±0.25 | X.X° | :±1° |
| X.XX | :±0.20 | X.XX° | :±0.5° |

| | | | | | | |
|---|---|---|---|---|---|---|
| DRAWM NAME: | HX PZ2.54-2x11P WZ | | | | | |
| SIZE | A4 | SCALE | N:1 | PROUCT NO. | | |
| REV | A | UNIT | mm | PROJECT | | PAGE 1/1 |
| DRAW: 黄彬 | 2022/04/24 | CHECKED: 张伟 | 2022/04/24 | APPROVED: 罗小春 | 2022/04/24 | |

| No. of | DIM.A | DIM.B | No. of | DIM.A | DIM.B | No. of | DIM.A | DIM.B | No. of | DIM.A | DIM.B |
|---|---|---|---|---|---|---|---|---|---|---|---|
| 1 | 0.00 | 2.54 | 11 | 25.40 | 27.94 | 21 | 50.80 | 53.34 | 31 | 76.20 | 78.74 |
| 2 | 2.54 | 5.08 | 12 | 27.94 | 30.48 | 22 | 53.34 | 55.88 | 32 | 78.74 | 81.28 |
| 3 | 5.08 | 7.62 | 13 | 30.48 | 33.02 | 23 | 55.88 | 58.42 | 33 | 81.28 | 83.82 |
| 4 | 7.62 | 10.16 | 14 | 33.02 | 35.56 | 24 | 58.42 | 60.96 | 34 | 83.82 | 86.36 |
| 5 | 10.16 | 12.70 | 15 | 35.56 | 38.10 | 25 | 60.96 | 63.50 | 35 | 86.36 | 88.90 |
| 6 | 12.70 | 15.24 | 16 | 38.10 | 40.64 | 26 | 63.50 | 66.04 | 36 | 88.90 | 91.44 |
| 7 | 15.24 | 17.78 | 17 | 40.64 | 43.18 | 27 | 66.04 | 68.58 | 37 | 91.44 | 93.98 |
| 8 | 17.78 | 20.32 | 18 | 43.18 | 45.72 | 28 | 68.58 | 71.12 | 38 | 93.98 | 96.52 |
| 9 | 20.32 | 22.86 | 19 | 45.72 | 48.26 | 29 | 71.12 | 73.66 | 39 | 96.52 | 99.06 |
| 10 | 22.86 | 25.40 | 20 | 48.26 | 50.80 | 30 | 73.66 | 76.20 | 40 | 99.06 | 101.60 |