


## ■ Specifications:

- Votage rating:250V AC/DC
- Current rating：2. 5-1.0A AC/DC
- Withstanding voltage:800V AC/minute
- Temperature range:-25℃~+85℃
- Insulation resistance:≥1000MΩ
- Contact resistance:≤10mΩ
- After environmental testing:≤20mΩ

X2006 T-P SN
① ②③ ④

① XKB Series No.
② Category:T-terminal
③ Material:Phosphor bronze
④ Plating Category :SN-Bright Tin Plating
V01:All Gold Flash




Section A-A
Scale:1:1




Section B-B
Scale:1:1




| | | | | | |
|---|---|---|---|---|---|
| X2006T-PV01 | Phosphor bronze | AWG#22~28 | 1.5mm(Max) | Gold Flash | X2006H |
| X2006T-PSN | Phosphor bronze | AWG#22~28 | 1.5mm(Max) | Stamping Before Pating:30u"Ni MIN;70" Sn MIN | X2006H |
| PART N0 | Material | Wire Range | Insulation O.D. | Finish | Suitable XKB Terminal |

广东星坤科技股份有限公司
生效
交付
文件工程章

| MARK | DESCRIPTION | DATE | REVISED | APPROVED |
|---|---|---|---|---|
| | | | | |
| | | | | |
| | | | | |
| | | | | |

REVISIONS

www.helloxkb.com

| | | | |
|---|---|---|---|
| XKB | ANGLAR | ±5° | |
| | L≤4 | ±0.2 | |
| | 4<L≤16 | ±0.3 | |
| | 16<L≤63 | ±0.4 | |
| | L>63 | ±0.5 | |

UNSPECIFIED TOLERANCES

| | | | | | |
|---|---|---|---|---|---|
| DSND | | DATE | | SCALE: N/A | MODEL TYPE: X2006T-PSN |
| DWN | | DATE | | VIEW: | PART NO.: |
| CHKD | | DATE | | UNIT: mm/in | DWG NO.: |
| APPD | | DATE | | SIZE: A4 | |

XKB INDUSTRIAL PRECISION CO.,LIMITED

| WEIGHT | SHEET | REVISION |
|---|---|---|
| | 1/1 | A0 |