

HSF

NOTES:

Current Rating: 5.0 AMP
Voltage Rating: 250V AC/DC
Temperature Range: -25℃ to +85℃
Contact Resistance: 10mΩ Max.
Insulation Resistance: 1000MΩ Min.
Withstanding Voltage: 1000V AC/Minute
Material: PA66(UL94V-0)
Color: Black


Ordering Information

WF3001-2H XX B 01

Terminal Shape
H: HOUSING

No. of Pins
02-12P

Colour:
B: Black



Specification & Ordering Information:

Circuit	Part No.	Dimension	
		A	B
2X1	WF3001-2H01B01	3.86	---
2X2	WF3001-2H02B01	6.85	3.00
2X3	WF3001-2H03B01	9.85	6.00
2X4	WF3001-2H04B01	12.85	9.00
2X5	WF3001-2H05B01	15.85	12.00
2X6	WF3001-2H06B01	18.85	15.00
2X7	WF3001-2H07B01	21.85	18.00
2X8	WF3001-2H08B01	24.85	21.00
2X9	WF3001-2H09B01	27.85	24.00
2X10	WF3001-2H10B01	30.85	27.00
2X11	WF3001-2H11B01	33.85	30.00
2X12	WF3001-2H12B01	36.85	33.00

		OPERATION		DRAW Ding	DATE 2018/05/24	SCALE UNIT	FIT mm inch	PART NO. SEE TAB
		X.X	±0.40					
A1	2018/05/24	Add the drawing		CHECK	DATE	SIZE	A4	TITLE: 3.00mm DUAL ROW HOUSING
AO	2012/06/12	NEW		APPROVE	DATE	SHEET	1/2	
REV	DATE	MODIFICATION DESCRIPTION		CHANGE		PROJ.		Customer NO.


WCON

Http: www.wcon.com


WCON-Dongguan Tel: +86 769 85358920
WCON-Kunshan Tel: +86 512 57468408
Fax: +86 769 85358915
E-mail: sales@wcon.com

Fax: +86 512 57468468
E-mail: salesks@wcon.com


HSF




2x1P




2x2P




2x3P




2x4P




2x5P




2x6P




2x7P




2x8P




2x9P



2x10P



2x11P



2x12P

				OPERATION		DRAW Ding	DATE 2018/05/24	SCALE	FIT	PART NO. SEE TAB	 Http: www.wcon.com WCON—Dongguan Tel: +86 769 85358920 WCON—Kunshan Tel: +86 512 57468408 Fax: +86 769 85358915 Fax: +86 512 57468468 E-mail: sales@wcon.com E-mail: salesks@wcon.com
				X.X	±0.40		CHECK	DATE	UNIT		
A1	2018/05/24	Add the drawing	——	X.XX	±0.25	APPROVE			DATE	SIZE	
AO	2012/06/12	NEW	——	X.XXX	±0.15		Angle DIM	TOL		SHEET	
REV	DATE	MODIFICATION DESCRIPTION	CHANGE							PROJ.	