BZG1-2RN2

Overview

MICRO SWITCH BZG/BZH Series Enclosed Switches, Top Roller Arm Actuator, Adjustable with Steel Roller, 1NC/1NO SPDT Snap Action, 1/2 in - 14NPT conduit.
MICRO SWITCH BZG/BZH switches have a neoprene seal gasket betwe

View More

view all BZG1-2RN2 literature
view distributor inventory
sample request
email technical support
start a chat we're offline
get support
email sales
find a distributor
email this page

Technical Specifications

Availability	**Global**
Release Force	**1,67 N [6 oz] min.**
Overtravel (OT)	**5,56 mm [0.219 in] min.**
Product Type	**Enclosed Switches**
Circuitry	**1NC 1NO SPDT Snap Action**

Operating Force (OF)	**2,78 N to 5,56 N [10 oz to 20 oz]**
Pretravel (PT)	**4,78 mm [0.188 in] max.**
Differential Travel (DT)	**0,15 mm [0.006 in] max.**
Actuator	**Top Roller Arm**
Supply Voltage	**125 Vac, 250 Vac, or 480 Vac/125 Vdc/250 Vdc**

View More

View documents in: English

Documents

TITLE	DOCUMENT TYPE	LANGUAGE	SIZE
JPG **BZG1-2RN2 highres photo**	Photo	--	2MB
JPG **BZG1-2RN2 lowres photo**	Photo	--	138KB
PDF **PK 88173: BZE6/V6 and BZG/H Enclosed Switches**	Installation Instructions	English	657KB
PDF **MICRO SWITCH Limit Switches Comparison**	Product Range Guide	English	460KB

View More

Product Features

- Cast aluminum housing
- Side or flange mount
- UL Recognized, file #E12252
- Grounding screw
- Sealed to NEMA 1, 3, 4, 13

Applications

- Packaging equipment
- Special machinery
- Textile machinery
- Conveyors
- Construction machinery and equipment
- Printing trades machinery
- Overhead cranes and hoists

This site uses cookies to simplify and improve your usage and experience of this website. Cookies are small text files stored on the device you are using to access this website. If you ignore this message and continue without changing your browser settings, we will assume that you are consenting to our use of cookies. For further information on our use of cookies, please see our Privacy Statement.

Don't show this message again