BZG1-2RN34

Overview

MICRO SWITCH BZG/BZH Series Enclosed Switches, Top Plunger Actuator, 1NC/1NO SPDT Snap Action, 1/2 in - 14NPT conduit.
MICRO SWITCH BZG/BZH switches have a neoprene seal gasket betwe

View More

view all BZG1-2RN34 literature
view distributor inventory
sample request
email technical support
start a chat we're offline
get support
email sales
find a distributor
email this page

Technical Specifications

Availability	Global
Release Force	2,78 N [10 oz] min.
Differential Travel (DT)	0,05 mm [0.002 in] max.
Actuator	Top Plunger
Supply Voltage	125 Vac, 250 Vac, or 480 Vac/125 Vdc/250 Vdc

Operating Force (OF)	4,17 N to 10,84 N [15 oz to 39 oz]
Overtravel (OT)	5,56 mm [0.219 in] min.
Product Type	Enclosed Switches
Circuitry	1NC 1NO SPDT Snap Action
Housing Material	Zinc Die-Cast

View More

View documents in: English

Documents

TITLE	DOCUMENT TYPE	LANGUAGE	SIZE
PK 88173: BZE6/V6 and BZG/H Enclosed Switches	Installation Instructions	English	657KB
MICRO SWITCH Limit Switches Comparison	Product Range Guide	English	460KB
Sensors and Switches in Front Loaders	Application Note	English	169KB
Enclosed Switches BZG/BZH Series	Catalog Information	English	386KB

View More

Product Features

- Cast aluminum housing
- Side or flange mount
- UL Recognized, file #E12252
- Grounding screw
- Sealed to NEMA 1, 3, 4, 13

Applications

- Packaging equipment
- Special machinery
- Textile machinery
- Conveyors
- Construction machinery and equipment
- Printing trades machinery
- Overhead cranes and hoists

This site uses cookies to simplify and improve your usage and experience of this website. Cookies are small text files stored on the device you are using to access this website. If you ignore this message and continue without changing your browser settings, we will assume that you are consenting to our use of cookies. For further information on our use of cookies, please see our Privacy Statement.

Don't show this message again