THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 2019
© COPYRIGHT 1999 TE Connectivity. All Rights Reserved. ALL RIGHTS RESERVED.

LOC	DIST

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	REVISED PER EO P17504	10DEC2001	ST	RDR
	C	REVISED PER EO P20851	25MAR2011	ST	RDR
	C1	REVISED PER PCN E-19-016328	18OCT2019	JA	IG
	C2	REVISED PER PCN E-21-001566	11FEB2021	MK	IG





3D VIEW

TE INTERNAL PN	DEUTSCH PN
1027-001-0800	1027-001-0800
1027-002-0800	1027-002-0800
1027-006-0800	1027-006-0800
1027-014-0800	1027-014-0800

2. ALL PART NUMBERS ARE IN ACCORDANCE WITH RoHS STANDARDS.

1 PART INFORMATION:

PART NUMBER	MATERIAL	HOLE DIAMETER
1027-001-0800	STAINLESS STEEL	.433 [11.0]
1027-002-0800	STEEL-ZINC PLATE	.512 [13.0]
1027-006-0800	STAINLESS STEEL	.512 [13.0]
1027-014-0800	STEEL-ZINC PLATE	.323 [8.2]

NOTES:

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES [mm]

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±.025 [0.64]
4 PLC ±
ANGLES ±0° 30′0″

MATERIAL 1

FINISH 1

DWN S.THEIS 09NOV1999
CHK B.BYFORD 23MAR2011
APVD S.BEARD 15MAR2011
PRODUCT SPEC
APPLICATION SPEC 114-151009
WEIGHT 10.5g

TE Connectivity

NAME METAL CLIP / MOUNTING BRACKET FOR 8 WAY RECEPTACLE DT SERIES

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	4AFU8	C-1027-001/002-006-014-0800	-

CUSTOMER DRAWING | SCALE 3:1 | SHEET 1 OF 1 | REV C2

1470-19 (3/11)