REVISIONS					
REV	NUMBER	DESCRIPTION	DWN	CHK	DATE
A		DESIGN			



ITEM NO.	PART NUMBER	DESCRIPITION	QTY.
④	套管	黑色热缩套管，OD:2.0MM	AS
③	端子	国产I-PEX 0.81 三代端子，镀金	1
②	接头	SMA母头母针,4脚半牙(牙长5mm),带凹槽,镀金,外螺纹内孔	1
①	同轴线	RF0.81cable同轴线，OD:0.8mm	AS

NOTES:

1. ELECTRICAL:
   1.1. VOLTAGE RATING:DCV 300V 10MS
   1.2. CONDUCTANCE RESISTANCE: 3.0 OHM/MAX.
   1.3. INSULATION RESISTANCE: 5.0M OHM/MIN.
   1.4. THE CABLE SHOULD BE 100% ELECTRICAL TEST
   1.5. IT SHOULD BE NO ANY OPEN/SHORT, MISWIRING AND INTERMITTENT FAILURES.
2. MATERIAL:
   2.1. SEE TABLE
3. ALL COMPONENTS ARE RoHS COMPLIANT.

深圳市金航标电子有限公司

ALL DIMENSION ARE IN MM

COMPUTER GENERATED IN SOLIDWORKS

DO NOT SCALE THIS DRAWING

PROJECTION

DRAWN	Jamy	DATE	2022-12-12
ENG.			
MFG.			
Q.A.			

GENERAL TOLERANCE FOR

ANGLES	X.X	X.XX	X.XXX
± 1°	± 0.3	± 0.25	± 0.150

KH-IPEX3-SMAKWE5-RG0.81-B090H

SIZE	Number	REV
B		A

SCALE: Free | TYPE | SHEET 1 OF 1

CUSTOMER P/N: