

Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE±0.05)



SPECIFICATIONS
Rated Current:3.0AMP
Contact Resistance:20mΩMax
Withstand Voltage:1000V AC/DC
Insulation Resistance:1000MΩMin
Operation Temperature:-40°c to +105°c

Contact Material:Brass
Contact Plating:Au or Sn Over Ni
Insulator Material:Polyester(UL94V-0)
Standard: PA6T
Max.Processing Temp: 230°C for 30-60 seconds
(260°C for 5 seconds)





P =With Post



默认=W/O Post



Dimension antitheses list				
ITEM	PA	PB	W	L
Standard	6.00	3.20	7.50	9.20

Ordering Information

PZ 254 - * - N - * - * - ** - * - P

- No.of Rows: 1=Single Row; 2=Dual Row; 3=Triple Row; 4=Quadruple Row
- No.of Pins: 2-40Pin
- Type: 2-直针; W-弯针; S-立贴; WS-弯贴; WW-反弯
- Length (塑高)
- Contact Plating: G0:Gold Flash; G1:1u" Gold; G2:3u" Gold; G3:5u" Gold; G4:10u" Gold; G5:15u" Gold; G6:30u" Gold; S0:Gold Flash/Tin; S1:Tin
- Packing: R=Reel +Cap (编带+盖)
- Post (带柱)

			GENERL TOLERANCE	制 图 DRAWING		深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD			
			DIM TOL	审 核 CHECK					
			X.X ±0.30	批 准 APPROVAL		产品名称 TITLE	2.54 双排 排针 贴片 编带+盖 (塑高2.5)	版 本 REV.	A
1	初版发行		X.XX ±0.20	比 例 SCALE		产品料号 PART NO.	PZ254-2-N-S-2.5-XX-R(L9.2)	单 位 UNITS	mm
序号 No.	变更内容 MODIFY CONTENT	日 期 MODIFY DATE	X.XXX ±0.10	投 影 Projection		材 料 MATERIAL		页 次 SHEET	1/1
			Angle ±3.0°						