



30mm BlackMax, Epoxy Coated Corrosion Resistant Metal Operator, Round Push-Pull Operator Non-Illuminated Mushroom Head Cap Large 2 1/2" (63.5 mm)  
 Plastic, Blue 3 Position Momentary UL Listed, CSA Certified NEMA 1,3,3R,4,4X,12,13 & Automotive Standards

design of the product	Actuator round
<b>Enclosure</b>	
number of command points	1
delivery state as a kit	No
<b>Actuator</b>	
material of the actuating element	plastic
type of unlocking device	without
number of switching positions	3
<b>Front ring</b>	
product component front ring	Yes
design of the front ring	standard
material of the front ring	metal
color of the front ring	black
<b>Holder</b>	
material of the holder	Metal
<b>General technical data</b>	
product component	
• light source	No
degree of pollution	1
protection class IP	IP66
<b>Ambient conditions</b>	
ambient temperature	
• during operation	-35 ... +70 °C
• during storage	-40 ... +85 °C
<b>Installation/ mounting/ dimensions</b>	
shape of the installation opening	round
<b>Certificates/ approvals</b>	
<b>Further information</b>	
Siemens has decided to exit the Russian market (see here). <a href="https://press.siemens.com/global/en/pressrelease/siemens-wind-down-russian-business">https://press.siemens.com/global/en/pressrelease/siemens-wind-down-russian-business</a>	
Siemens is working on the renewal of the current EAC certificates. Please contact your local Siemens office on the status of validity of the EAC certification if you intend to import or offer to supply these products to an EAC relevant market (other than the sanctioned EAEU member states Russia or Belarus).	
Information on the packaging <a href="https://support.industry.siemens.com/cs/ww/en/view/109813875">https://support.industry.siemens.com/cs/ww/en/view/109813875</a>	
Information- and Downloadcenter (Catalogs, Brochures,...) <a href="https://www.siemens.com/ic10">https://www.siemens.com/ic10</a>	
Industry Mall (Online ordering system) <a href="https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=US2:52BP3V5">https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=US2:52BP3V5</a>	
Cax online generator <a href="http://support.automation.siemens.com/WW/CAxorder/default.aspx?lang=en&amp;mlfb=US2:52BP3V5">http://support.automation.siemens.com/WW/CAxorder/default.aspx?lang=en&amp;mlfb=US2:52BP3V5</a>	
Service&Support (Manuals, Certificates, Characteristics, FAQs,...) <a href="https://support.industry.siemens.com/cs/ww/en/ps/US2:52BP3V5">https://support.industry.siemens.com/cs/ww/en/ps/US2:52BP3V5</a>	
Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)	

**last modified:**

5/31/2021 