MICRO SWITCH
FREEPORT ILLINOIS, U.S.A
A DIVISION OF HONEYWELL
FED. MFG. CODE 91929

ASSEMBLY– TOGGLE SWITCH

CATALOG LISTING
206AT11



NOTE-
1- UNIT INCLUDES CAT. LIST. 11HM1 **BASIC SWITCH**
2- LEVER HAS SATIN FINISH

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION

CHARACTERISTICS

ELECTRICAL DATA

CONTACT ARRANGEMENT
S P D T

LINE VOLTAGE	INDUCTIVE LOAD	RESISTIVE LOAD
SEA LEVEL 70,000 FT 28 VDC	1 AMP	3 AMP
SEA LEVEL 115 (400 CYCLE)	1 AMP	1 AMP

SCALE FULL

DO NOT SCALE PRINT

TOLERANCES
APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR REFERENCE. UNLESS NOTED, TOLERANCES ARE ±

	DIM. mm	TOL. mm/in	DIM. in	TOL. mm/in
NO PLACES	X	1/.04		
ONE PLACE	X.X	0.4/.016	X.X	0.8/.03
TWO PLACES	X.XX	0.15/.006	X.XX	0.38/.015
THREE PLACES			X.XXX	0.13/.005
ANGLES				

DESIGN UNITS: SI METRIC ☐ US CUSTOMARY ☒

WEIGHT

REPLACES
RELEASE NO. PR-9560
DRAWING NUMBER 206AT11 M
ISSUE 4 7 5

REVISIONS

A	OBS C047639	S M A 1 MAY 80
B	RE-IN PR-9560	C E B 11 DEC 80
C	CO 50566-B	WJM 10 MAY 82
D	CO 58771	K A G 14 FEB 86
E	CO-68001	SAV 21 JUL 90
F	C071132	TSM 16 OCT 91

CHECK
CHECK
CHECK
CHECK
DRAWN C E B 11 DEC 80

FO-52848-A