SHEET 1 OF 1





SPECIFICATIONS

FUNCTION:
1P1T OFF-(ON) + 1P1T ON-(OFF)

RATINGS:
ANSI/UL 1054 and CAN/CSA C22.2 No. 55 (E194579):
18A 125VAC [cURus]
12A 250VAC [cURus]

OPERATING FORCE:
3.0kgf±0.5kgf

ELECTRICAL LIFE:
6,000 Cycles [cURus]

APPROVALS:

RoHS COMPLIANT

COLORS

BODY:
White

ACTUATOR:
Black

LOCK:
Black

SCHEMATIC



POSITION 1 (MAINTAINED) POSITION 2 (MOMENTARY)

E·SWITCH

HY15-6Y7-211-0000

REFERANCE	REV.	DATE	BY
BODY	A	09/07/10	CAB
COLORS	A	09/07/10	CAB
SPECIFICATIONS	A	09/07/10	CAB

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

REV.	DESCRIPTION	PCR	DATE	DRAWN BY
B	Removed TUV reference information	21770	01/19/15	rc
A	INITIAL RELEASE	PCR00054	09/07/30	CAB

DIMENSIONS: INCHES [MILLIMETERS]
GENERAL TOLERANCES: ±0.020 [±0.5] / ±1°
SCALE: DRAWING NOT TO SCALE
PROJECTION:

DRAWING NUMBER	DATE	REVISION
34-HY156Y72110000	JULY 30, 2009	B