受控 CONTROLLED DOCUMENT					
编号 P/N	40-97XXM	版本 Rev	02	日期 Rel'd Date	Jul11,11

Description: 97 Series Solder Style Panel & Cable Mount D-Sub Connectors

Part No: 40-97xxM

Application: For Cable

Crimp Tool: N/A

Impedance: N/A

Fequency Range: 0-15 MHz

Material: Housing Steel Nickel plated

Insulator PBT+Fiber-glass UL94-V0 White

Contact Cu-alloy, Gold plated

RoHS Compliance: Yes

Technical Detail: N/A

P/N	Pins	A	B	C	D
40-9709M	9	30.80	24.99	16.92	19.20
40-9715M	15	39.15	33.32	25.25	27.70
40-9725M	25	53.00	47.04	38.96	41.10
40-9737M	37	69.30	63.50	55.42	57.30





DRAWING NO. 40-97XXM

REVISIONS

01	OFFICIAL RELEASE						
	02-20-09	TW	BY	T			
02	CHANGE SHELL PLATING FROM YELLOW ZINC TO NICKEL; CHANGE DIMENSIONS: 3.50MAX TO 3.8REF; D DIMENSION FOR 40-9725M FROM 41.28 TO 41.10; ADD DIMENSIONS: 1.25MAX; 5.6MAX;						
	03-25-11	JJ	JJ	D			ECO-11-0055

CUSTOMER COPY

TOLERANCE UNLESS OTHERWISE SPECIFIED		DRAWN BY JEAN.JIN	DATE 03-25-11
DECIMALS	mm	CHECKED BY JEAN.JIN	DATE 03-25-11
X	± 0.5		
X.X	± 0.3	APPROVED BY DONALD	DATE 03-25-11
X.XX	± 0.1		
ANGLES	± 0.5°	U/M mm	

THIS DRAWING WAS PRODUCED BY COMPUTER, DO NOT SCALE DRAWING OR UPDATE MANUALLY.

cinch CONNECTIVITY SOLUTIONS a bel group

TITLE 97 SERIES SOLDER STYLE PANEL & CABLE MOUNT D-SUB CONNECTORS

SHEET	DRAWING NO.	SIZE
1 OF 1	40-97XXM-CUST	A

SOLID EDGE RESELLER COPY