

REV. 0

DCO 170403

COIL: @ 25°C

RESISTANCE 100 OHMS ± 10%

NOMINAL VOLTAGE 40.0 mADC

MUST OPERATE 20.0 mADC

MUST RELEASE 10.0 mADC MAX, 2.0 mADC MIN

ENVIRONMENT:

VIBRATION 10 CPS TO 2000 CPS @ 15 g's

SHOCK 100 g's 6 MS. DURATION

TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE TIME 15 MS MAX
RELEASE TIME 10 MS MAX
CONTACT BOUNCE 2 MS MAX

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO 2A
28 VDC RESISTIVE 100,000 OPERATIONS

DR. PBB 2/16/01 | CK. TLG 02-16-01

CII Technologies
advanced control electronic solutions

CUST. QPL

CUST. NO. M5757/13-084 REV.

3SAT RELAY

3SAT1301A2

F-718 REV 3