

PRODUCT-DETAILS

SN201 L-C16

SN201 L-C16 Miniature circuit breaker - 1+NP - C - 16 A



Model	SN201 L-C16
Part number	2CSS245101R0164
EAN	8012542088653
SN201 L-C16 Miniature circuit breaker - 1+NP - C - 16 A	
The SN201 series miniature circuit breaker is a 1P+N device in 1 module for the protection of circuits against overload and short circuit. Neutral is on the right	

Standard	IEC/EN 60898-1
Curve	C
Rated voltage (U _r)	230 V AC
Rated current (I _n)	acc. to IEC 60898-1 230 V
Rated short-circuit current (I _{sc})	acc. to IEC/EN 60664-1 500 V
Rated breaking capacity (I _{imp})	4 kV
Rated making capacity	2 kV
Rated short-circuit capacity	4 kV
Rated frequency	AC
Rated current (I _n)	16 A
Rated short-circuit capacity	(230 V) 4.5 kA

额定短路分断能力 (I _{cu})	(230 V) 6 kA
额定短路容量 (I _{cs})	(230 V AC) 4.5 kA
额定频率 (f)	50/60 Hz
额定功率	3.6 W
额定电压	Arbitrary
额定电流	Red ON / Green OFF
额定寿命	3
额定寿命	10000 cycle
额定寿命	20000 cycle
额定寿命	1+N
额定寿命	1
Number of Modular Spacings per DIN Rail	1
额定寿命	III
额定寿命	Right
额定寿命	1.2 N·m
额定寿命	Auxiliary contact Signal contact / auxiliary contact Shunt trip Undervoltage release
额定寿命	Toggle - Insulation group IIIA, black, sealable in ON-OFF positions
额定寿命	Insulation group II, RAL 7035
额定寿命	Cage Terminal
额定寿命	Any
Accessories Available	Yes
额定寿命	Flexible 1 ... 10 mm² Rigid 1 ... 16 mm²
额定寿命	11 mm
额定寿命	Screw Terminals

额定寿命	
额定寿命	-25...55 °C
额定寿命	Operation -25 ... 55 °C
额定寿命	30 °C
额定寿命	IP20
额定寿命	2
额定寿命	28 cycles ;with 55 °C / 90-96 % ;and 25 °C / 95-100 %
额定寿命 IEC 60068-2- 6	0.35mm or 5g - 20 cycles at 5...150...5 Hz without load
额定寿命 IEC 60068-2-27	30g 2 shocks 13 ms
RoHS	Following EU Directive 2011/65/EU
RoHS	9AKK106713A5572
额定寿命	refer to RoHS information
Conflict Minerals Reporting Template (CMRT)	9AKK108468A3363

mm(000000)	1
mm	0.018 m
mm	0.085 m
mm	0.069 m
mm	0.110 kg
mm (t ₂)	69 mm

mm	
mm	1 piece
10000	box 6 piece
1000 mm	0.684 kg
E-Number (Finland)	3217711

mmmmmmmmmm	
mmmm - CE	9AKK106713A5572

Installation	
mmmm	No document needed

Popular Downloads	
mmmmmmmm	2CSC400002D0209

mm	
ETIM 8	EC000042 - Miniature circuit breaker (MCB)
ETIM 9	EC000042 - Miniature circuit breaker (MCB)
WEEE mm	5. Small Equipment (No External Dimension More Than 50 cm)
WEEE B2C / B2B	Business To Consumer
CN8	85362010
e	V11.0 : 27141901
mmmm	F

mm	
mmmm	→ mmmmm → Miniature Circuit Breakers MCBs → mmmmm

