

TTL

SSI FUNCTIONS (Cont'd)

Item	Function ⁽¹⁾	9000 Series 8 ns/10 mW	Low Power Schottky 54LS/74LS 5 ns/2 mW	Std. TTL 9N 54/74 10 ns/10 mW	High Speed 54H/74H 6 ns/22 mW	High Speed Schottky 54S/74S 3 ns/19 mW	Logic/Connection Diagram ⁽²⁾	Packages ⁽³⁾
Exclusive NOR Gate								
1	Quad 2-Input (OC)	—	74LS266	9386 (8242)	—	—	D94	3I,6A,9A
AND-OR Gates								
2	Dual 4-2 Input	—	—	—	—	9S42	D25	4L,6B,9B
3	2-2-2-3 Input (Exp)	—	—	—	54H/74H52	—	D26	3I,6A,9A
AND-OR-INVERT Gates								
4	Dual 2-2 Input (Exp)	9005	—	54/7450	54H/74H50	—	D27	3I,6A,9A
5	Dual 2-2 Input	—	54LS/74LS51	54/7451	54H/74H51	54S/74S51	D28	3I,6A,9A
6	2-2-2-3 Input (Exp)	9008	—	54/7453	54H/74H53	—	D29	3I,6A,9A
7	2-2-2-3 Input	—	—	54/7454	54H/74H54	—	D30	3I,6A,9A
8	2-2-3-3 Input	—	54LS/74LS54	—	—	—	D31	3I,6A,9A
9	2-2-3-4 Input	—	—	—	—	74S64	D32	6A,9A
10	2-2-3-4 Input (OC)	—	—	—	—	74S65	D32	6A,9A
11	4-4 Input (Exp)	—	—	—	54H/74H55	—	D33	3I,6A,9A
12	4-4 Input	—	54LS/74LS55	—	—	—	D34	3I,6A,9A
Gate Expanders								
13	Triple 3-Input	—	—	—	54H/74H61	—	D35	3I,6A,9A
14	Dual 4-Input	9006	—	54/7460	54H/74H60	—	D36	3I,6A,9A
15	2-2-3-3 AND-OR	—	—	—	54H/74H62	—	D37	3I,6A,9A
Buffer Gates and Drivers								
16	Quad Buffer (3S)	—	54LS/74LS125	54/74125	—	—	D66	3I,6A,9A
17	Quad Buffer (3S)	—	54LS/74LS126	54/74126	—	—	D67	3I,6A,9A
18	Hex (3S)	—	54LS/74LS365	—	—	—	D68	4L,6B,9B
19	Hex Inverter (3S)	—	54LS/74LS366	—	—	—	D69	4L,6B,9B
20	Hex (3S)	—	54LS/74LS367	—	—	—	D70	4L,6B,9B
21	Hex Inverter (3S)	—	54LS/74LS368	—	—	—	D71	4L,6B,9B

1. OC = open collector, 3S = 3-state.

2. The logic symbols located in the Logic/Connection Diagram Section are for the DIP version.

3. For specific availability or delivery information on a given package and temperature grade, consult the Fairchild O.E.M. Price List or call the local sales representative or distributor.