


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	03/23/2021	PHOSPODAR

WIRING MAP


J1	J2	J3	COLOR	J3	J4
		12	BLUE		1
		11	ORANGE		2
		10	GREEN		3
		9	BROWN		4
12			GRAY		5
11			WHITE		6
2			RED		7
1			BLACK		8
		4	YELLOW		9
		3	PURPLE		10
		2	ROSE		11
		1	AQUA		12
12			BLUE w/TRACER		1
11			ORANGE w/TRACER		2
10			GREEN w/TRACER		3
9			BROWN w/TRACER		4
10			GRAY w/TRACER		5
9			WHITE w/TRACER		6
4			RED w/TRACER		7
3			BLACK w/TRACER		8
4			YELLOW w/TRACER		9
3			PURPLE w/TRACER		10
2			ROSE w/TRACER		11
1			AQUA w/TRACER		12



PART NUMBER	LENGTH METERS (FEET)	BREAKOUT METERS (FEET)
MPF308212OM4Z-CA1	1.0 (3.28)	0.3 (1.00)
MPF308212OM4Z-CA3	3.0 (9.84)	0.6 (2.00)
MPF308212OM4Z-CA5	5.0 (16.40)	0.6 (2.00)
MPF308212OM4Z-CA10	10.0 (32.81)	0.6 (2.00)

NOTES:

1. MPO CONNECTOR MULTIMODE ASSEMBLY POLISH TYPE: UPC.
2. ALL CONNECTORS ACCOMPANIED WITH A DUST CAP INSTALLED (NOT SHOWN).
3. PACKAGING: INDIVIDUALLY PACKAGE EACH ASSEMBLY IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]		APPROVALS	DATE	 an INFINITI brand		50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936	
OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0		DRAWN BY DZINN	03/23/2021			CATEGORY FIBER OPTICS	
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] .XX = ± .02 [.5] .XXX = ± .005 [.13]		CHECKED BY DFRISIELLO	03/23/2021	PRODUCT DESCRIPTION FIBER AG CONV HARNESS, 3xMPO8 (F) TO 2xMPO12 (F)		SIZE A	
THIRD-ANGLE PROJECTION 		APPROVED BY PHOSPODAR	03/23/2021	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		CAGE CODE 43321	
		COLOR VARIATIONS MAY OCCUR		ITEM NO. MPF308212OM4Z-CA		SCALE: NONE	
				CAD FILE: MPF308212OM4Z-CA.SLDDRW		SHEET 1 OF 1	