


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE
PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE
WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	1/25/22	JJOHNSTON





PART NUMBER	LENGTH METER [FEET]
FCA-SLCAMTRJUD2	2.0 [6.56]
FCA-SLCAMTRJUD5	5.0 [16.40]
FCA-SLCAMTRJUD10	10.0 [32.81]
FCA-SLCAMTRJUD15	15.0 [49.21]

NOTES:

1. LC CONNECTOR 2 ASSEMBLY POLISH TYPE: APC.
2. MTRJ CONNECTOR ASSEMBLY POLISH TYPE: UPC.
3. ALL CONNECTORS ACCOMPANIED WITH A DUST CAP INSTALLED (NOT SHOWN).
4. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED.

REGULATORY COMPLIANCE:

EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS ± 1/32 .XX = ± .02 [.5] ANGLES ± 1° .XXX = ± .005 [.13] THIRD-ANGLE PROJECTION 	APPROVALS	DATE	 an INFINITI® brand 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936	
	DRAWN BY DMAY	01/19/2022		CATEGORY FIBER OPTICS
	CHECKED BY JJOHNSTON	1/25/22		
	APPROVED BY JJOHNSTON	1/25/22		
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		PRODUCT DESCRIPTION FIBER OPTIC PATCH CORD SM G652D DUPLEX LC/APC-MTRJ/UPC ARMORED 4.8mm LSZH BLACK		
COLOR VARIATIONS MAY OCCUR	SIZE A	CAGE CODE 43321		ITEM NO. FCA-SLCAMTRJUD
		SCALE: NONE	CAD FILE: FCA-SLCAMTRJUD.SLDDRW	SHEET 1 OF 1