


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE  
PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE  
WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	01/25/2022	JJOHNSTON



PART NUMBER	LENGTH METER [FEET]
FCA-SFCUFCUD2	2.0 [6.56]
FCA-SFCUFCUD5	5.0 [16.40]
FCA-SFCUFCUD10	10.0 [32.81]
FCA-SFCUFCUD15	15.0 [49.21]

#### NOTES:

- FC CONNECTOR 4 ASSEMBLY POLISH TYPE: UPC.
- ALL CONNECTORS ACCOMPANIED WITH A DUST CAP INSTALLED (NOT SHOWN).
- CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED.

#### REGULATORY COMPLIANCE:

EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]  OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0  ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5]      FRACTIONS ± 1/32 .XX = ±.02 [.5]      ANGLES ± 1° .XXX = ±.005 [.13]  THIRD-ANGLE PROJECTION 	APPROVALS	DATE	 an INFINITI® brand  50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936
	DRAWN BY DMAY	1/18/22	
	CHECKED BY JJOHNSTON	1/25/22	
	APPROVED BY JJOHNSTON	1/25/22	
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	CATEGORY  FIBER OPTICS		PRODUCT DESCRIPTION FIBER OPTIC PATCH CORD SM G652D DUPLEX FC/UPC-FC/UPC ARMORED 4.8mm LSZH, BLACK
COLOR VARIATIONS MAY OCCUR	SIZE <b>A</b>	CAGE CODE <b>43321</b>	
	ITEM NO. FCA-SFCUFCUD	REV. <b>A</b>	
	SCALE: NONE	CAD FILE: FCA-SFCUFCUD.SLDDRW	