


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	1/25/2022	JJOHNSTON



PART NUMBER	LENGTH METER [FEET]
FCA-SLCALCAD2	2.0 [6.56]
FCA-SLCALCAD5	5.0 [16.40]
FCA-SLCALCAD10	10.0 [32.81]
FCA-SLCALCAD15	15.0 [49.21]

NOTES:

- LC CONNECTOR 4 ASSEMBLY POLISH TYPE: APC.
- ALL CONNECTORS ACCOMPANIED WITH A DUST CAP INSTALLED (NOT SHOWN).
- CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED.

REGULATORY COMPLIANCE:

EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]		APPROVALS		DATE		 an INFINITE® brand 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936
OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0		DRAWN BY DMAY		1/18/22		
		CHECKED BY JJOHNSTON		1/25/22		
		APPROVED BY JJOHNSTON		1/25/22		
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS .XX = ± .02 [.5] ± 1/32 .XXX = ± .005 [.13] ANGLES ± 1°		CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		CATEGORY FIBER OPTICS		
THIRD-ANGLE PROJECTION 		COLOR VARIATIONS MAY OCCUR		PRODUCT DESCRIPTION FIBER OPTIC PATCH CORD SM G652D DUPLEX LC/APC-LC/APC ARMORED 4.8mm LSZH BLACK		
		SIZE A		CAGE CODE 43321	ITEM NO. FCA-SLCALCAD	REV. A
		SCALE: NONE		CAD FILE: FCA-SLCALCAD.SLDDRW		SHEET 1 OF 1