

NOTE

MATERIAL & FINISH

INSULATOR: PBT 30%GF (UL94 V-0)

CONTACT: BRASS, GOLD OR TIN OVER NI

ELECTRICAL & MECHANICAL

CURRENT RATING: 1.5A

CONTACT RESISTANCE: 20mΩ MAX.

INSULATION RESISTANCE: 1000MΩ MIN.

WITHSTAND VOLTAGE: 500V AC/DC

OPERATION TEMPERATURE: -40°C TO +105°C





Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE±0.05)



———		new		2015/5/3	A	瀚源
ECN BO.		DESCRIPTION.		DATE.	REV.	
DESIGNED	CHECKED	APPROVAL	DRAWING NUMBER		SCALT: 1/2	SCALE: 3:1
Mikey	Tom	Jerry	PART NAME	HY2005WV-N-2xXXP	UNLESS OTHERWISE SPECIFIED,TOLERANCE:	X. ±0.25 X.x ±0.20 X.xx ±0.15 ANGULAIR ±3
			MODEL NAME	HY2005WV-N-2xXXP		
			3RD ANGLE PROJ	HanElectricity Co.,LTD		FILE.NO.