CHIP COMMON MODE CHOKE

CND-tek
磁联达

- High Common Mode Impedance at High Freqency.
- Excellent Noise Suppression Performance.
- Small Size and Low Profile,Surface Mount Type.
- Operating Temperature Range: -40 °C to +105°C.
- RoHS Compliant.

Part Number	Electrical Specifications@25°C					
	Common Mode Impedance(Ω)	Test Frequency (MHz)	DCR (Ω Max)	Rated Voltage (V)	Rated Current (mA)Max.	IR M(Ω Min)
ACM3225F-2-501T10 H	500±25%	100	0.20	50	1000	10

MECHANICAL



A(mm)	B(mm)	C(mm)	D1(mm)	D2(mm)
3.2±0.20	2.5±0.20	2.2±0.20	1.0±0.10	0.7±0.10

SCHEMATICS



TAPING AND PACKING





Type	A(mm)	B(mm)	C(mm)	D(mm)	E(mm)	H(mm)
13"x8mm	330±2	87±1	2.7±0.5	100±1	1.9±0.2	8±0.5

Quantity (pcs) :
2000 PCS PER REEL
5 REELS PER CARTON
10000 PCS PER CARTON

Shenzhen magnetic Lianda Electronics Co., LTD

Address: 505, West Block, No. 221, Niucheng Road, Niucheng Village, Baiwang Community, Xili Street, Nanshan District, Shenzhen
Tel:0755-27652992 29016433 E-mail: sales1@cd-tek.com Website:www.cd-tek.com