


① 15P 塑膠本體

SPECIFICATIONS:
INSULATION RESISTANCE:1000Mohm MIN
WITHSTANDING VOLTAGE:1000V AC FOR ONE MINUTE
OPERATING TEMPERATURE RANGE:-40°C~+85°C

MATERIAL AND FINISH:
INSULATOR: ABS OR HIPS(UL94V-0)
CONTACT: COPPER ALLOY
FINISH: Zn PLATED OR Cr PLATED




② 塑膠螺母




③ 塑殼螺絲




④ 卡片

PART NO.

Z-SUB B0*0 002* ** 0

NO OF CONTACTS
B=15PIN

FITTING PLATED
N=NI
P=COLOR Zn
Q=BLUE Zn
R=Cr3+

INSULATOR COLOR
0=BLACK
8=GREY
L=LVORY WHITE

INSULATOR MATERIAL/PLATED
D=ABS, NO PLATED
E=ABS, Cr PLATED
H=HIPS, NO PLATED




⑤ 卡片螺絲




⑥ 線夾螺絲




⑦ 線夾

ENGINEERING CORPORATION NEXTRONICS
ISSUE DATE
2018/09/27
This file is automatically issued by EPDM and is not valid without the issue date

| REV. | DESCRIPTION | DATE |
|---|---|---|
| A2 | ADD LOGO A2=1 | 9/26'18 |
| A1 | MODIFY | 3/9'16 |
| A | NEW RELEASED | 7/28'11 |

| UNITS ■mm □INCH | | |
|---|---|---|
| GENERAL TOLERANCES: (UNLESS SPECIFIED) | mm | INCH |
| 4 PLACE | ± *** | ±. *** |
| 3 PLACE | ± *** | ±. *** |
| 2 PLACE | ± 0.05 | ±. *** |
| 1 PLACE | ± 0.10 | ±. *** |
| ANGULAR: | X°± 1° | .X°±** |

NAME: D-SUB HOOD 15P 塑膠殼及配件
PART NO: Z-SUBB0B0002***0
APPD: Peter 2018/09/27
CHKD: Peter 2018/09/27
DRAWN: Lu 2018/09/26

NEXTRONICS ENGINEERING CORP.
TITLE: CUSTOMER DWG
DWG NO: 010-0000-921 C
SCALE: 1/1 SHEET: 1/1 REV.: A2

A3
D-PRD-034