

## Specification Sheet

Part Number: TYHCA-Z

Handi-Cards have a split backing so that a portion of the liner can be removed to expose the markers for easy dispensing.

Handi-Cards are kitted on the card so that specific markers can be removed without affecting the other markers on the card.

Markers are pre-printed so no additional post printing is required, saving time and money.

Label material is a conformable cloth that ensures markers stay on wires and cables for the life of the application.



Handi-Card Wire and Cable Markers, 0.25" x 1.5", Sequence Letter A-Z, 36/Card, TYHC, White, 25/pkg

Article Number 598-00190

Type TYHCA-Z

Color White (WH)

Quantity Per pack

Product Description HellermannTyton Handi-Cards are easy release pre-printed cloth markers, on a plastic card, with a strong adhesive for a long lasting bond on wire and cable. The markers are available in Solid format where each marker on the card contains the same legend and Sequence format where each marker on the card contains a different number or letter which is usually printed in sequence from lowest to highest in sort order.

Short Description	Handi-Card Wire and Cable Markers, 0.25" x 1.5", Sequence Letter A-Z, 36/Card, TYHC, White, 25/pkg
Global Part Name	TYHCA-Z-TYHC-WH
Length L (Imperial)	1.5
Length L (Metric)	38.1
Width W (Imperial)	0.25
Width W (Metric)	6.35
Bundle Diameter Min (Imperial)	.13
Bundle Diameter Min (Metric)	3.40
Bundle Diameter Max (Imperial)	0.29
Bundle Diameter Max (Metric)	7.50
Height H (Imperial)	1.5
Height H (Metric)	38.1
Outside Diameter Max (Imperial)	0.29
Outside Diameter Min (Metric)	3.40
Outside Diameter Min (Imperial)	0.13
Outside Diameter Max (Metric)	7.50

Material	Vinyl Cloth (TYHC)
Material Shortcut	TYHC
Adhesive	Rubber
Halogen Free	No
UV Resistant (Yes/No)	No
Adhesive Operating Temperature	-40°F to +248°F (-40°C to +120°C)
Operating Temperature	-40°F to +248°F (-40°C to +120°C)
Reach Compliant (Article 33)	No
ROHS Compliant	Yes
Package Quantity (Imperial)	25
Package Quantity (Metric)	25
Customs Number	5903103000
Labels per Column	1
Labels per Row	36

## About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. ([www.hellermann.tyton.com](http://www.hellermann.tyton.com)).

© 2023 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)