REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A			2024.12.16	











Voltage rating:50V AC/DC
:50V AC/DC
Current rating:0.5A
0.5A
Insulation resistance:1000MΩ Min
1000MΩ Min
Withstanding voltage:≥300V AC/minute
≥300VC/
Temperature range:−45 −+125
−45 −+125

PART NO.:

X1270 H−2xXX A−PT AUSN

Series No
Category:H−HSG
Row No−Pin No:2xXX−2x05P~2x50P
A:1.27x2.54mm
Material:PT−Nylon PBT UL94V−0
Planting Category:AUSN−AUSN Plating

PINS	A	B	C
2x05P	11.25	8.35	5.08
2x07P	13.79	10.89	7.62
2x08P	15.06	12.12	8.89
2x10P	17.60	14.70	11.43
2x13P	21.41	18.51	15.24
2x15P	23.95	21.05	17.78
2x16P	25.22	22.32	19.05
2x17P	26.49	23.59	20.32
2x20P	30.30	27.40	24.13
2x25P	36.65	33.75	30.48
2x30P	43.00	40.10	36.83
2x34P	48.08	45.18	41.91
2x50P	68.40	65.50	62.23

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERAuCES	

XKB Connection

DESIGN		VIEW:	MODEL TYPE: 1.27mm BTB Style Connectors
CHECKED		UNIT: mm/in	PART NO.: X1270H−2xXXA−PTAUSN
APPROVED		SIZE: A4	DWG NO.:

XKB INDUSTRIAL PRECISION CO.,LIMITED

SCALE	PAGE	REVISION
N/A	1/1	A1