

Product data sheet

Specifications



Pre wired connectors XZ, elbowed female, M12, 4 pins, cable PUR 5 m

XZCP1241L5

Main

Range of product Telemecanique Cabling components

Accessory / separate part category Cabling accessory

Accessory / separate part type Pre-wired connectors

Series name General purpose

Complementary

Electrical connection Elbowed female connector M12, 4 pins

Cable connector fixing Screw-on

Collar material Metal

Status LED Without

Cable length 5 m

Cable outer diameter 5.2 mm

Cable composition 4 x 0.34 mm²

Wire insulation material PUR

[Ue] rated operational voltage 250 V AC
300 V DC

[In] rated current 4 A

Contact resistance 5000 µOhm

Minimum insulating resistance 1 GΩ

Net weight 0.19 kg

Environment

IP degree of protection IP65
IP67
IP69K

Product certifications cULus

Ambient air temperature for operation -40...80 °C static
-5...80 °C flexing

Ambient air temperature for storage -40...80 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.0 cm
Package 1 Width	18.5 cm
Package 1 Length	19.0 cm
Package 1 Weight	155.0 g
Unit Type of Package 2	S02
Number of Units in Package 2	20
Package 2 Height	15.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	3.428 kg
Unit Type of Package 3	P06
Number of Units in Package 3	320
Package 3 Height	77.0 cm
Package 3 Width	80.0 cm
Package 3 Length	60.0 cm
Package 3 Weight	55.6 kg


Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
California proposition 65	WARNING: This product can expose you to chemicals including: Diisobutyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Contractual warranty

Warranty	18 months
-----------------	-----------


Dimensions



L : Lenght of cable

Connections and Schemes

Connector



BN : Brown

BK : Black

BU : Blue

WH : White

Recommended replacement(s)