

Power Cord, C19 to NEMA L5-20P - Heavy-Duty, 20A, 125V, 12 AWG, 10 ft. (3.05 m), Black

MODEL NUMBER: P045-010









Heavy-duty extension cord transforms a C20 plug into a locking NEMA L5-20P plug and extends an existing connection up to 10 ft.

Features

Heavy-Duty Extension Cable Connects Devices That Require a Heavy-Gauge ConnectionThis heavy-duty extension cord features 12 AWG wire suitable for high power connections, making it a reliable solution for large server applications that require a higher-rated, heavier-gauge cable. This C19 to L5-20P cord transforms a non-locking plug into a locking plug and can be used to connect a high-output device to a wall outlet or a PDU or UPS with L5-20R outlets. It is also a recommended replacement or upgrade of a standard power cord provided by the device's manufacturer. The 10-ft. (3.05 m) length allows you great flexibility in placing equipment with respect to the power outlet.

Locking L5-20P Connector Helps Prevent Accidental Disconnection and Expensive

DowntimeHaving a cable come loose accidentally can mean the loss of power and costly downtime. The locking connector helps you avoid such danger, protecting critical equipment by maintaining a secure link without failure. The locking cable is also invaluable when moving equipment in a rack or removing equipment from tight areas, ensuring the power cord always stays connected.

Highlights

- 10-ft. (3.05 m) length allows great flexibility in placing devices in relationship to AC outlet
- Heavy-duty cable replaces or upgrades standard power cord provided by manufacturer
- Thick 12 AWG wire gauge manages high power levels required for larger equipment
- Locking connector maintains secure link to avoid loss of power and costly downtime

Applications

- Connect devices to a power outlet up to 10-ft. (3.05 m) away in your office or workspace
- Transform a non-locking C20P plug into a locking L5-20P plug to prevent a power loss due to accidental disconnection
- Extend an existing power connection up to 10-ft. (3.05 m) to more easily place a device or reach a power source in a rack
- Update or replace the standard power cord provided by a device's original manufacturer

Package Includes

 P045-010 C19 to L5-20P Heavy-Duty Extension Cord, 10ft. (3.05 m), Black

Specifications

OVERVIEW		
UPC Code	037332140937	
Device Compatibility	Server; UPS; PDU	
Country/Region	North America	
INPUT		
Maximum Input Amps	20	
Voltage Compatibility (VAC)	125	



Black	
Black	
Black	
Black	
PVC	
VW-1	
SJT	
11mm	
3	
12	
3.31	
10	
3.05	
10.98 x 7.00 x 0.50	
27.89 x 17.78 x 1.27	
1.72	
0.78	
-4° to 140°F (-20° to 60°C)	
-4° to 140°F (-20° to 60°C)	
10% to 65% RH, Non-Condensing	
NEMA L5-20P	
IEC-320-C19	
No	
STANDARDS & COMPLIANCE	
cUL Listed; UL Listed	



Product Compliance	RoHS	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	Lifetime limited warranty	



© 2023 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.