



SECTION A–A
SCALE 1:1

Note:
1. Material:
   1.1 Housing: thermoplastic high temp.UL94V–0; Color: natural.
   1.2 Latch: thermoplastic high temp.UL94V–0; Color: black.
   1.3 Terminal: copper alloy.
   1.4 Fitting Nail: copper alloy.
2. Finsh:
   2.1 Terminal:
   Underplating: Au/matt Tin overall.
   2.2 Fitting Nail:
   Underplating: matt Tin overall.
3. Product must comply HF RoHS specification.
4. Product No:

AFA02–S ** H * A – 00

CKTS
CONTACTS TYPE
F:Lower
H:Double Lower
PLATING
1:Gold flash 1u"
2:Gold flash 2u"
3:Gold flash 3u"
B:Bright–Tin 90–120u"
C:Matt–Tin 90–120u"
PACKING
A:Tape&Reel
C:Tube
REMARKS
HF:Halogen free

CKTS	DIM A	DIM B	DIM C
4	3.00	5.10	8.90
5	4.00	6.10	9.90
6	5.00	7.10	10.90
7	6.00	8.10	11.90
8	7.00	9.10	12.90
9	8.00	10.10	13.90
10	9.00	11.10	14.90
11	10.00	12.10	15.90
12	11.00	13.10	16.90
13	12.00	14.10	17.90
14	13.00	15.10	18.90
15	14.00	16.10	19.90
16	15.00	17.10	20.90
17	16.00	18.10	21.90
18	17.00	19.10	22.90
19	18.00	20.10	23.90
20	19.00	21.10	24.90
21	20.00	22.10	25.90
22	21.00	23.10	26.90
23	22.00	24.10	27.90
24	23.00	25.10	28.90
25	24.00	26.10	29.90
26	25.00	27.10	30.90
27	26.00	28.10	31.90
28	27.00	29.10	32.90
29	28.00	30.10	33.90
30	29.00	31.10	34.90







RECOMMENDED P.C.B PATTERN LAYOUT



RECOMMENDED FPC/FFC DIMENSION

Rev 版本	Change Description 变更内容	Date 日期	Revisor 制/修订人
A	初版发行	2011/03/23	Allan

CUSTOMER DRAWING

Tolerance Unspecified (未注公差)
0.0 ±0.15 0°. ±5°
0.00 ±0.10 0°.0 ±3°
0.000 ±0.05 0°.00 ±1°

Project View (投影视角)

Size(图幅): A4
Unit(单位): MM
Scale(比例): 1 : 1
Page(页数): 1 OF 1
Rev(版本): A

LXW 连兴旺电子(深圳)有限公司
LXWCONN ELECTRONICS(SHENZHEN)CO.,LTD

Product Name(产品名称): 1.0Pitch H=2.0 FPC Easy-on R/A D/C TypeG SMT CONN
Product No(产品料号): AFA02-S**H**-**
Designer(设计): Allan 03/23'11
Checked(审核):
Approved(核准):

PDF !"# "pdfFactory Pro" $#%&' (www.fineprint.cn