REV.	DESCRIPTION	ECN NO.	NAME	DATE





SECTION A–A











LOCK CONFIGURATION(锁扣位置)

Part No	CKT	A	B	C
WF-MX1.25-2PB1	2	1.25	3.20	4.30
WF-MX1.25-3PB1	3	2.50	4.45	5.55
WF-MX1.25-4PB1	4	3.75	5.70	6.80
WF-MX1.25-5PB1	5	5.00	6.95	8.05
WF-MX1.25-6PB1	6	6.25	8.20	9.30
WF-MX1.25-7PB1	7	7.50	9.45	10.55
WF-MX1.25-8PB1	8	8.75	10.70	11.80
WF-MX1.25-9PB1	9	10.00	11.95	13.05
WF-MX1.25-10PB1	10	11.25	13.20	14.30
WF-MX1.25-11PB1	11	12.50	14.45	15.55
WF-MX1.25-12PB1	12	13.75	15.70	16.80
WF-MX1.25-13PB1	13	15.00	16.95	18.05
WF-MX1.25-14PB1	14	16.25	18.20	19.30
WF-MX1.25-15PB1	15	17.50	19.45	20.55
WF-MX1.25-16PB1	16	18.75	20.70	21.80
WF-MX1.25-17PB1	17	20.00	21.95	23.05
WF-MX1.25-18PB1	18	21.25	23.20	24.30
WF-MX1.25-19PB1	19	22.50	24.45	25.55
WF-MX1.25-20PB1	20	23.75	25.70	26.80



序号	品名	材质
1	A型卧式DIP型WTB胶芯 1.25 Pitch S/T Wire To Board Housing DIP(H=3.2)	LCP UL94V-0 本色 Natural
2	A型卧式DIP型WTB端子 1.25 Pitch S/T Wire To Board Terminal DIP(H=3.2)	铜合金/表面镀锡 Copper Alloy/ Tin Plating

技术指标(Technical Index):

1.塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象.
(The surface of the plastic parts should be smooth,no rough edges,no obvious shrinkage,defects,cracks and other phenomena)

2.锁扣窗口:2~3PIN为1个,≥4PIN为2个.
(Lock Configuration:2 to 3Pin is 1,≥4Pin is 2)

3.温度范围(Temperature range):-25°C~+85°C.

4.额定电压(Rated voltage):125V,AC/DC(=等效).

5.接触电阻(Contact resistance):≤0.02Ω.

6.绝缘电阻(Insulation resistance):≥100MΩ

GENERAL TOLERANCE						DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD		BXCONN®
DIM.	TOL.					TITLE: 1.25 Pitch A型弯针WTB		
x.	±0.50							
x.x	±0.20							
x.xx	±0.10							
GENERAL	ANGLE:					DWG. NO.: WF-MX1.25-XPB1	CHECKED: MAX	
x.°	±1°							
						PART NO.: WF-MX1.25-XPB1	DRAWN: ELLA	
		UNIT: mm	SCALE: none	SHEET: 1of 1	DWG. SIZE: A4	LAYER: bxconn	APPROVED: WILL	

REV.	DESCRIPTION	ECN NO.	NAME	DATE







NOTE(注):

1.10 SPROCKET HOLE PITCH CUMULATIVE TOLERANCE ±0.2mm.
(10片孔距累积公差±0.2mm.)

2.CARRIER CAMBER NOT TO EXCEED 1mm IN 100mm.
(载带拱/弧形MAX:1/100mm.)

3.ALL DIMENSIONS MEET EIA-481 REQUIREMENTS.
(所有的尺寸要满足协会EIA-481规范.)

4.MATTRIAL:CLEAR ANTISTATIC PS.
(载带材料:透明 PS.)

5.THICKNESS:0.40±0.05mm.(载带厚度:0.40±0.05mm.)

6.PACKING LENGHT PER REEL: 10.56 METERS.(每卷包装长度:10.56米.)

7.COMPONENT LOAD PER REEL:850 PCS.(每卷包装数量:850只,前后各空包15只.)

8.纸箱装箱以不超过装箱线为准,空余位置用塑料泡沫及保尼龙填充.

9.纸箱分小、中、标准型3种规格型号:装箱为整箱(左下包装量)采用标准型纸箱包装,未达到整箱数量以产品量适当采用小型或中型纸箱包装.

纸箱型号 Carton Type	小型 Small Size	中型 Medium	标准型 Standard
高度 Hight (CM)	7.5	15	32













CKT (1.25mm pitch)	W	PCS/RELL	RELL/CARTON	SUM(PCS)
2	16	850	14	11900
3				
4	24	850	10	8500
5				
6				
7				
8				
9				
10				
11	32	850	8	6800
12				
13				
14				
15				
16	44	850	6	5100
17				
18				
19				
20				

CKT (1.25mm pitch)	B0	W	F	S
2	4.60	16	7.50	
3	5.85			
4	7.10	24	11.50	
5	8.35			
6	9.60			
7	10.85			
8	12.10			
9	13.35			
10	14.60			
11	15.85	32	14.2±0.10	28.45
12	17.10			
13	18.35			
14	19.60			
15	20.85			
16	22.10	44	20.2±0.15	40.45
17	23.35			
18	25.85			
19	28.35			
20	30.85			

GENERAL TOLERANCE

DIM.	TOL.
x.	±0.50
x.x	±0.25
x.xx	±0.15
GENERAL ANGLE:	
x.°	±2°

DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD

BXCONN®

TITLE: 1.25 Pitch A型弯针WTB包装

DWG. NO.: WF-MX1.25-XPB1 | CHECKED: MAX

PART NO.: WF-MX1.25-XPB1 | DRAWN: ELLA

UNIT:	SCALE:	SHEET:	DWG. SIZE:	LAYER:	APPROVED:
mm	none	1of 1	A4	bxconn	WILL