REV.	DESCRIPTION	ECN NO.	NAME	DATE



PIN	A	B	C
B0401FSV15-10P	4.6	1.6	1.0
B0401FSV15-12P	5.0	2.0	
B0401FSV15-20P	6.6	3.6	
B0401FSV15-24P	7.4	4.4	1.2
B0401FSV15-30P	8.6	5.6	1.5
B0401FSV15-34P	9.4	6.4	2.3
B0401FSV15-40P	10.6	7.6	3.2
B0401FSV15-50P	12.6	9.6	
B0401FSV15-60P	14.6	11.6	
B0401FSV15-70P	16.6	13.6	
B0401FSV15-80P	18.6	15.6	
B0401FSV15-90P	20.6	17.6	
B0401FSV15-100P	22.6	19.6	





The product is high	H
B0401FSV15-XP	1.45
B0401FSV20-XP	1.95
B0401FSV24-XP	2.40
B0401FSV29-XP	2.90
B0401FSV34-XP	3.40
B0401FSV39-XP	3.90

SPECIFICATIONS
1.CURRENT RATING: 0.3A .
2.VOLTAGE RATING 30V AC/DC.
3.TEMPERATURE RANGE:-35°CTO+85°C
4.CONTACT RESISTANCE: 90mΩ MAX.
5.INSULATION RESISTANCE:50 MΩ MIN.
6.WITHSTANDING VOLTAGE:100V AC/MINUTE.



RECOMMENDED PCB LAYOUT

GENERAL TOLERANCE ±0.05

GENERAL TOLERANCE		
DIM.	TOL.	
x.	±0.50	
x.x	±0.35	
x.xx	±0.25	
GENERAL ANGLE:		
X.°:	±2°	
X.X°:	±1°	

DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD

BXCONN®

TITLE: 0.40MM BTB SOCKET

DWG. NO.: B0401FSV15-XP

CHECKED: MAX

PART NO.: B0401FSV15-XP

DRAWN: ELLA

UNIT:	SCALE:	SHEET:	DWG. SIZE:	LAYER:	APPROVED:
mm	none	1of 1	A4	bxconn	WILL