

Specification Sheet

Part Number: 115-00030



The heavy duty Speedy tie features a specially designed head and patented trigger to allow for repeated use in temporary bundling applications.

Additional design feature on the head allows excess strap to be tucked away after installation.

Releasable Cable Tie, 29.6" Long, 200 lb Tensile Strength, PA66HIRH(S), Black, 5/pkg

Article Number	115-00030
----------------	-----------

Type	SpeedyTie (RTT750HR)
------	----------------------

Color	Black (BK)
-------	------------

Quantity Per	pcs.
--------------	------

Product Description	HellermannTyton releasable cable ties offer a release feature in the head allowing for easy access to wire bundles when changes or temporary bundling are necessary. The head design guarantees high tensile strength even after repeated use.
---------------------	--

Short Description	Releasable Cable Tie, 29.6" Long, 200 lb Tensile Strength, PA66HIRH(S), Black, 5/pkg
-------------------	--

Global Part Name	SpeedyTie (RTT750HR)-PA66HIR(S)-BK
------------------	------------------------------------

Minimum Tensile Strength (Imperial)	200.0
Minimum Tensile Strength (Metric)	888.0
Length L (Imperial)	29.6
Length L (Metric)	752.0
Identification Plate Position	none
Releasable Closure	Yes
Tie Closure	plastic pawl
Variant	Inside Serrated
Width W (Imperial)	0.51
Width W (Metric)	13.0
Bundle Diameter Min (Imperial)	1.6
Bundle Diameter Min (Metric)	40.0
Bundle Diameter Max (Imperial)	8.3
Bundle Diameter Max (Metric)	210.0
Thickness T (Imperial)	0.075
Thickness T (Metric)	1.9

Material	Polyamide 6.6, high impact modified, scan black (PA66HIR(S))
Material Shortcut	PA66HIR(S)
Flammability	UL 94 HB
UV Resistant (Yes/No)	No
Operating Temperature	-40°F to +176°F (-40°C to +80°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	5
Package Quantity (Metric)	5
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

