

Specification Sheet


Part Number: IMP210C2

Identification Marker Plates can be marked with a permanent pen, printed labels or hot stamped for a wide variety of labeling options.

Any size bundle diameter can be marked because it is only dependent upon the length of the cable tie selected, provided the cable tie width does not exceed .29".

The marker plates are stamped from nylon, making them a durable and long term method of identification.

The mounting holes are positioned to allow the marker to be mounted as a flag, tag or wrapped around the cable or bundle for a wide variety of installed positions.



Identification Marker Plate, 2.0" x .75", Nylon, White, 100/pkg

Article Number	151-42229
----------------	-----------

Type	IMP2
------	------

Color	White (WH)
-------	------------

Quantity Per	bag
--------------	-----

Product Description	Identification Marker Plates can be mounted in any direction, either vertically or horizontally as flags, tags, or wraparound identification plates. They can be hot stamped or marked with HellermannTyton marking pens (T82-S), thermal transfer labels, or laser labels. The markers are manufactured from nylon and are white in color.
---------------------	---

Short Description	Identification Marker Plate, 2.0" x .75", Nylon, White, 100/pkg
Global Part Name	IMP2-PA66-WH
Length L (Imperial)	2
Length L (Metric)	50.8
Fixation Method	Others
Identification Plate Position	attached to bundle
Variant	Other
Width W (Imperial)	2.0
Width W (Metric)	19.3
Thickness T (Imperial)	0.016
Thickness T (Metric)	0.4
Height H (Imperial)	0.75
Height H (Metric)	19.05
Cable Tie Width Max (Imperial)	0.18
Cable Tie Width Max (Metric)	4.80

Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Flammability	UL 94 V-2
Halogen Free	Yes
UV Resistant (Yes/No)	No
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909988
Weight (Metric)	0.06
Weight (Imperial)	0.132

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global

customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin.
(www.hellermann.tyton.com).

© 2023 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)