SAMZO | REAC/ROHS

REV	ECN NO	DESRIPTION	DESIGN	APPROVAL	DATE
A1	NEW	Replace frame			2018.06.15











主要技术参数、性能
The Main Thchnology Performance

额定电流、电压 Rate voltage.current	50mA DC12V
接触电阻 Contact resistance	≤100mΩ
按力 Operating force	±50gf
行程 Travel	0.20±0.10mm
绝缘电阻 Insulated resistance	≥100MΩ
介电强度 Dielectric strength	≥250VAC/1min

J	4	B	*	*	*	*	*	1	L
A	B	C		D		E	F	G	H

A.系列：J-6*6mm系列
B.贴装方式：4-立式贴片
C.规格：B-4P
D.操作高度：043-4.3mm/060-6.0mm/115-11.5mm/210-21.0mm/(4.3-25.0)
E:操作力度:1-120gf/2-180gf/3-260gf/4-350gf
F:操作寿命：1-100,000次/2-500,000次/3-1,000,000次
G:固定方式：1-无柱
H:物料编码：L:脚距9.0mm(确认待编)



电路图
CIRCUIT DIAGRAM



PCB.焊接图
PCB.WELDING DRAWING

ITEM	DESCRIPTION	MATERIAL	QTY	FINSH/COLOR					
E	Button	BRASS	1	Pickling					
D	Cover plate	SUS/201	1	Clean				GENERAL TOLERANCE	
C	Shrapnel	SUS/301	1	Silver plating				≥0~2<	±0.15
B	Subject	PPA	1	Black	DESIGN	WANGGUIFA	2018.06.12	≥2~5<	±0.25
A	Card	Phosphorous copper	1	Silver plating	CHECKED	ZHENGUILAN	2018.06.12	≥0~2<	±0.15
					APPROVED	LILIANJIANG	2018.06.14	≥5	±0.35

FIRST VIEW



SCALE	1:1	UNIT	mm

The copyright belongs to samzo parts [China] Co., Ltd. please use the material after samzo parts agree to authorize. The final right of interpretation belongs to samzo parts.
WWW.KKK-JP.COM

SAMZO COMPONENTS
Electronic switch and connector manufacturer

TITLE:: 6.0*6.0*H mm 4P-LT
DWG NO: J4BXXX-1806-P39
PART NO: J4BXXX1806
MODEL NO: J4B-***-*-*-1L
NAME: TACT SWITCH