NO.	ECN NO.	DESCRIPTION	DATE
1			

客户图



Note:

1: Material(材料)：
- Barrel: Brass C3602（针管：黄铜 C3602 ）
- Plunger: Brass C3604 （针头：黄铜 C3604）
- Spring: SUS304 （弹簧：SUS304）

2: Plating(电镀)：
- Barrel: 3u' Au over 50~80u' Ni(针管：镀金3u'，镍底50~80u'。)
- Plunger: 3u' Au over 50~80'u Ni（针头：镀金3u'，镍底50~80u'。）
- Spring: Gold plated（弹簧：铍铜镀金）

3: Electrical(电气特性)：
- Rated Current & Voltage: DC 12V;4A（额定电压&电流: 直流12V,4A）
- Contact Resistance: 50 mohm Max. at working height.
- 接触电阻：最大50毫欧（在工作高度状态下）

4: Mechanical(机械性能)：
- Force: 100g±20% at working height. (100g±20%在工作高度时）。
- Durability: 10.000 cycles(min)（寿命：10000次）

5: WorkTemperture(工作环境)：
- Withstanding Higt Temperature: 280℃
- Operational Temperature: −40℃~ +85℃

深圳市鑫扬泽电子有限公司

HTTP://WWW.XYZPOGOPIN.COM

TEL:0755-28773277 FAX:0755-28891353

SCALE:	N/A	UNIT	mm
SHEET:	1 of 1	PROJECTION	
DATE:	2018.04.12	VER.	A.0

THE UNMARKED TOLERANCE ARE AS BELOW :

LENGTH		ANGLE	
X.XX	±0.05mm	X.XX	±0.50°
X.X	±0.10mm	X.X	±1.00°
X.	±0.20mm	X.	±2.00°

DESIGNED BY:		DWG. NO.	YZB0006-25073-01
CHECKED BY:		TITLE:	Pogo pin
APPROVED BY:			